




- 1 TIN PL .000150 MIN THK PER ASTM B 545
- 2 PART NO: 324466; .243 LB.
PART NO: 1-324466-0; .243 LB.
PART NO: 2-324466-1; .243 LB.
PART NO: 2-324466-2; .269 LB.
- 3 RED COLOR CODE
- 4 CLEANED, UNPLATED
- 5 .045 MAX BURR ALLOWED INSIDE THE WIRE BARREL ID IN AREA OF SIGHT HOLE.

OBSOLETE	1.07	1.32	2.64	△	450-550 MCM	COPPER ASTM-B-75 ANNEALED	2-324466-2
	1.07	1.07	2.41	△△			2-324466-1
				△			1-324466-0
				△			324466
	"C"	"B"	"A"	FINISH	WIRE RANGE	MATERIAL	PART No

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

DK SCHRUM

4/24/89

CHK

MS FEHER

4/24/89

APVD

WJ VOCKROTH

11/8/89

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

△

CUSTOMER DRAWING

TE Connectivity

SPLICE, BUTT, AMPPOWER

WIRE SIZE: 500 MCM

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=324466

—

SCALE

SHEET

REV

2:1

1 OF 1

R