



CONTACT CONFIGURATION
TIMING (BBM) NON-SHORTING



ISOMETERIC



NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT MATERIAL: SILVER
5. CONTACT RATING: 0.3A @125VAC
6. OPERATING FORCE 800±300 GRAMS
7. OPERATING TEMP: -30°C TO 85°C
- ▲ 8. CIRCUIT SP: 3 POSITION 90° INDEX
9. DIELECTRIC STRENGTH: 500VAC-60 SEC.
- ▲ 10. HARDWARE SUPPLIED ON SWITCH:
LOCKWASHER, HEXNUT, STOP RING
11. ▲ DENOTES CRITICAL PARAMETER.

E-SWITCH®

B	15244	ADDED DIM. AND CHANGED NOTES 8,9,10	9/7/05	PH
A	15054	RELEASED FOR PRODUCTION	7/11/05	JB
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE KC56A38.001NLS

SCALE 1.5:1

DATE 7/11/2005

DR JB

DWG G511003

REV B