

3" Core Wire & Cable Materials:

Brady B-472 Topcoated Polyimide Wirewrap Material

Continued from previous page.





Diagram	Catalog #	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Write On Area Height F Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 1	THT-1-472-10-OR	Polyimide	Orange	0.750 (19.05)	0.250 (6.35)	0.800 (20.32)	-	3.350 (85.09)	4	10,000	R4300
Fig. 1	THT-2-472-10-OR	Polyimide	Orange	0.900 (22.86)	0.250 (6.35)	1.125 (28.6)	-	3.350 (85.09)	3	10,000	R4300
Fig. 1	THT-5-472-10-OR	Polyimide	Orange	1.000 (25.40)	0.500 (12.70)	1.075 (27.31)	-	3.350 (85.09)	3	10,000	R4300
Fig. 3	THT-259-472-OR	Polyimide	Orange	1.000 (25.40)	300 ft. (91.4 m)	-	-	1.200 (30.48)	1	1 roll cont.	R4306
Fig. 2	THT-29-472-10-OR	Polyimide	Orange	1.250 (31.75)	0.375 (9.50)	1.300 (33.02)	-	2.750 (69.85)	2	10,000	R4300
Fig. 3	THT-105-472-OR	Polyimide	Orange	1.500 (38.10)	300 ft. (91.4 m)	-	-	1.700 (43.18)	1	1 roll cont.	R4302
Fig. 3	THT-106-472-OR	Polyimide	Orange	2.000 (50.80)	300 ft. (91.4 m)	-	-	2.200 (55.88)	1	1 roll cont.	R4300
Fig. 3	THT-21-472-OR	Polyimide	Orange	3.000 (76.2)	300 ft. (91.4 m)	-	-	3.200 (81.28)	1	1 roll cont.	R4300
Fig. 1	THT-1-472-10-PK	Polyimide	Pink	0.750 (19.05)	0.250 (6.35)	0.800 (20.32)	-	3.350 (85.09)	4	10,000	R4300
Fig. 1	THT-2-472-10-PK	Polyimide	Pink	0.900 (22.86)	0.250 (6.35)	1.125 (28.6)	-	3.350 (85.09)	3	10,000	R4300
Fig. 1	THT-5-472-10-PK	Polyimide	Pink	1.000 (25.40)	0.500 (12.70)	1.075 (27.31)	-	3.350 (85.09)	3	10,000	R4300
Fig. 3	THT-259-472-PK	Polyimide	Pink	1.000 (25.40)	300 ft. (91.4 m)	-	-	1.200 (30.48)	1	1 roll cont.	R4306
Fig. 2	THT-29-472-10-PK	Polyimide	Pink	1.250 (31.75)	0.375 (9.50)	1.300 (33.02)	-	2.750 (69.85)	2	10,000	R4300
Fig. 3	THT-105-472-PK	Polyimide	Pink	1.500 (38.10)	300 ft. (91.4 m)	-	-	1.700 (43.18)	1	1 roll cont.	R4302
Fig. 3	THT-106-472-PK	Polyimide	Pink	2.000 (50.80)	300 ft. (91.4 m)	-	-	2.200 (55.88)	1	1 roll cont.	R4300
Fig. 3	THT-21-472-PK	Polyimide	Pink	3.000 (76.2)	300 ft. (91.4 m)	-	-	3.200 (81.28)	1	1 roll cont.	R4300
Fig. 1	THT-1-472-10-RD	Polyimide	Red	0.750 (19.05)	0.250 (6.35)	0.800 (20.32)	-	3.350 (85.09)	4	10,000	R4300
Fig. 1	THT-2-472-10-RD	Polyimide	Red	0.900 (22.86)	0.250 (6.35)	1.125 (28.6)	-	3.350 (85.09)	3	10,000	R4300
Fig. 1	THT-5-472-10-RD	Polyimide	Red	1.000 (25.40)	0.500 (12.70)	1.075 (27.31)	-	3.350 (85.09)	3	10,000	R4300
Fig. 3	THT-259-472-RD	Polyimide	Red	1.000 (25.40)	300 ft. (91.4 m)	-	-	1.200 (30.48)	1	1 roll cont.	R4306
Fig. 2	THT-29-472-10-RD	Polyimide	Red	1.250 (31.75)	0.375 (9.50)	1.300 (33.02)	-	2.750 (69.85)	2	10,000	R4300
Fig. 3	THT-105-472-RD	Polyimide	Red	1.500 (38.10)	300 ft. (91.4 m)	-	-	1.700 (43.18)	1	1 roll cont.	R4302
Fig. 3	THT-106-472-RD	Polyimide	Red	2.000 (50.80)	300 ft. (91.4 m)	-	-	2.200 (55.88)	1	1 roll cont.	R4300
Fig. 3	THT-21-472-RD	Polyimide	Red	3.000 (76.2)	300 ft. (91.4 m)	-	-	3.200 (81.28)	1	1 roll cont.	R4300
Fig. 1	THT-1-472-10-VT	Polyimide	Violet	0.750 (19.05)	0.250 (6.35)	0.800 (20.32)	-	3.350 (85.09)	4	10,000	R4300
Fig. 1	THT-2-472-10-VT	Polyimide	Violet	0.900 (22.86)	0.250 (6.35)	1.125 (28.6)	-	3.350 (85.09)	3	10,000	R4300
Fig. 1	THT-5-472-10-VT	Polyimide	Violet	1.000 (25.40)	0.500 (12.70)	1.075 (27.31)	-	3.350 (85.09)	3	10,000	R4300
Fig. 3	THT-259-472-VT	Polyimide	Violet	1.000 (25.40)	300 ft. (91.4 m)	-	-	1.200 (30.48)	1	1 roll cont.	R4306
Fig. 2	THT-29-472-10-VT	Polyimide	Violet	1.250 (31.75)	0.375 (9.50)	1.300 (33.02)	-	2.750 (69.85)	2	10,000	R4300
Fig. 3	THT-105-472-VT	Polyimide	Violet	1.500 (38.10)	300 ft. (91.4 m)	-	-	1.700 (43.18)	1	1 roll cont.	R4302
Fig. 3	THT-106-472-VT	Polyimide	Violet	2.000 (50.80)	300 ft. (91.4 m)	-	-	2.200 (55.88)	1	1 roll cont.	R4300
Fig. 3	THT-21-472-VT	Polyimide	Violet	3.000 (76.2)	300 ft. (91.4 m)	-	-	3.200 (81.28)	1	1 roll cont.	R4300
NOTICE BBP[®]11 PRINTER ONLY: The following part numbers ending with "-SC" are 1" Small Core Rolls specially designed for use in the BBP11 Printer and do not require the BBP11 media adaptor accessory. View page 82 for more information.											
Fig. 3	THT-105-472-SC	Polyimide	White	1.500 (38.10)	200 ft. (60.96 m)	-	-	1.700 (43.18)	1	1 roll cont.	R4313
Fig. 3	THT-21-472-SC	Polyimide	White	3.000 (76.2)	200 ft. (60.96 m)	-	-	3.200 (81.28)	1	1 roll cont.	R4313
Fig. 3	THT-105-472-YL-SC	Polyimide	Yellow	1.500 (38.10)	200 ft. (60.96 m)	-	-	1.700 (43.18)	1	1 roll cont.	R4313
Fig. 3	THT-21-472-YL-SC	Polyimide	Yellow	3.000 (76.2)	200 ft. (60.96 m)	-	-	3.200 (81.28)	1	1 roll cont.	R4313

Did You Know? - Technical Data Sheets

Looking for more information regarding a certain Brady material?

Brady offers online access to Technical Data Sheets for all Brady materials. View by a specific B-Number or search by relevant keywords.

Visit www.BradyID.com/techdata for more information.



View the Material Brands & Attributes Guide on page 4.

Benchtop Printer Ribbons on page 184.

Full Material Properties on page 187.

1-888-272-3946 | www.BradyID.com