

SPECIFICATIONS




Model Number: JQ12B4

Part Number: 19031089A

SPEC NUMBER: 260113781A00

April 22, 2005

Mechanical Drawing:



Motor:

Nominal Voltage	= 12 vdc
Operating Voltage Range	= 9 - 14 vdc
Nominal Running Current	= 2.26 Amps
Locked Rotor Current	= 4.0 Amps
Running Power	= 25.2 Watts
Average Speed	= 3400 rpm
Bearings	= Ball
Air Flow	= 235 cfm
Acoustic	= 54.3 dBA

Construction:

Venturi: Die-cast Aluminum, Black
Propeller: Plastic, Black, UL 94V-0

Life Expectancy:

This fan is designed for continuous duty life of 75,000 hours at 40°C.

Additional Features:

Brushless DC Motor	
Locked Rotor Protection	
Polarity Protected	
Automatic Restart Capability	
Operating Temperature:	-10°C to 70°C
Storage Temperature:	-40°C to 85°C

Termination:

2 Terminals

Agency Approvals:

UL, CE