

LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
G	14				E	REV,RDRW,& SM PKG PER 0720-0008-93	4-5-93	1AP DAP

METRIC

DIMENSIONS LISTED IN mm [INCHES]


AMP WIRE RANGE	 E13288 Listed
12-10 AWG SOLID OR STRANDED	12-10 AWG STRANDED
 LR7189 Certified	MILITARY P/N AND CLASS
12-10 AWG SOLID OR STRANDED	NOT APPLICABLE

- 1

STAMP AMP 12-10* APPROX AS SHOWN
- 2

MEETS EQUIVALENT REQUIREMENTS
OF ASTM B-152
- 3

MEETS EQUIVALENT REQUIREMENTS
OF MIL-T-10727



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

FOR APPLICATION
TOOLING INFORMATION

FOR ORDER ENTRY

PRODUCT INFORMATION CENTER
1-800-522-6752

TOOLING ASSISTANCE CENTER
1-800-722-1111

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
2.62-6.64mm² [5,180-13,100] CIR MILS
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± -
3 PLC DEC ± -
ANGLES ± -

MATERIAL
COPPER PER AMP SPEC 100-2
ANNEALED

FINISH
TIN PLATE
0.00254 [0.00100] MIN
THK PER AMP SPEC 112-16

DR 4-5-93
TA BRINKMAN
CHK 4-5-93
DA PATTERSON

APPD 4-5-93
DE MILLER

APPD 4-5-93
JL MECKLEY

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

50	LOOSE PIECE, BOX	8-36271-2
----	LOOSE PIECE	36271
QUANTITY	PACKAGE TYPE	PART NO

AMP AMP Incorporated
Harrisburg, PA 17105-3608

NAME
TERMINAL, RING TONGUE,
FLAG, SOLISTRAND™

SIZE
CAGE CODE
DRAWING NO
00779
C=36271

SCALE 10:1
SHEET 1 OF 1