



Ripac box type plug-in units, type I

Technical specifications:

Installation depth: 160 and 220 mm
Height: 3 U and 6 U
to IEC 60 297-3,
to accommodate:
individual connectors

Material:

Front panel: 2.5 mm aluminium,
natural anodised
Rear panel: 2 mm aluminium, natural anodised
Side panel sections: Extruded aluminium section,
natural anodised
Handle: Aluminium, natural anodised.
PCB holder: Plastic

Available upon request:

- Box type plug-in units in special sizes or with printing
- EMC box type plug-in units with EMC front panels




Accessories:



Covers,
see page 545.
Guide rails,
see page 512.
Individual components,
see page 542.

HP	a mm	B mm	b mm	c mm	C mm	d mm	e mm	f mm	Model No. RP		
									3 U	3 U	6 U
Board depth 160 mm											
6	32.2	–	20.3	27.5	–	171.5	122	167	3653.000	–	–
8	40.3	–	30.5	36.0	–	171.5	122	167	–	3653.010	–
10	50.5	35.6	40.6	46.2	–	171.5	122	167	–	3653.020	3653.100
12	60.6	45.7	50.8	56.4	–	171.5	122	167	–	3653.030	3653.110
14	70.8	55.9	60.9	66.5	–	171.5	122	167	–	3653.040	3653.120
21	106.3	91.4	96.4	102.0	86.3	171.5	122	167	–	3653.050	3653.130
28	141.9	127.0	132.0	137.6	121.8	171.5	122	167	–	3653.060	3653.140
42	213.1	198.1	203.2	208.8	193.0	171.5	122	167	–	3653.070	3653.150
Board depth 220 mm											
10	50.5	35.6	40.6	46.2	–	231.5	182	227	–	3653.200	3653.300
12	60.6	45.7	50.8	56.4	–	231.5	182	227	–	3653.210	3653.310
14	70.8	55.9	60.9	66.5	–	231.5	182	227	–	3653.220	3653.320
21	106.3	91.4	96.4	102.0	86.3	231.5	182	227	–	3653.230	3653.330
28	141.9	127.0	132.0	137.6	121.8	231.5	182	227	–	3653.240	3653.340
42	213.1	198.1	203.2	208.8	193.0	231.5	182	227	–	3653.250	3653.350
Supply includes											
Font panel									1	1	1
Handle									1	1	2
Side panels									1	2	2
Cover including rear panel									1	–	–
Rear panel									–	1	2
PCB holder									2	2	2
Assembly parts (set)									1	1	1


Section A – A
Board depth 160 mm



Section B – B
Type I, 3 U



Section A – A
Board depth 160 mm



Section B – B
Type I, 6 U

