


[Back to Overview](#)[Find a reseller](#)[Request](#)

Sample order

Standard poles sizes

02

[Order](#)

[Home](#) > [Products](#) > [Terminal blocks & headers](#) > [Spring clamp terminal blocks](#)
[pluggable](#)

SP145xxHBNC (ASP145)

- spring clamp terminal block, pluggable
- centerline 5.00 mm, direction of connection 90°
- fittable without loss of poles
- color black
- push-button, wire entry perpendicular or parallel to plug direction, three plugging directions

[check distributor inventory](#)

> Technical Data	insulating material class	CTI 225
> Part numbers (P/N)	Rated wiring solid wire [AWG]	0.08 - 1.5 mm ²
	Rated wiring stranded wire [AWG]	0.08 - 1.5 mm ²
> matching header	Rated wiring solid wire [AWG]	AWG 28 - 16
	Rated wiring stranded wire [AWG]	AWG 28 - 16
> Downloads	Clearance and creepage distances	3.2 mm
	degree of protection according to IEC 529	IP 20
	min. insul. strip length	7 mm
	Color	black
	Approvals	
	V / A / AWG	300 / 6 / 28 - 16
	13.5 A / 250 V / 4 kV / 3	/ 0.08 - 1.5 mm ² / IEC 61984

