



- | | |
|---|---|
| 1 | CAVITY LETTERS MARKED PER MIL-STD-130 WITH WHITE INK. |
| 2 | AMP INFORMATION MARKED PER MIL-STD-130. |
| 3 | PIGTAILS ARE SOLDERED DIPPED. |
| 4 | INSULATION CUT, BUT NOT REMOVED. |



A	_____	BROWN
B	_____	RED
C	_____	GREEN
D	_____	BLUE
E	_____	BLACK
F	_____	WHITE

	24.00 [609.6]	5-867472-2
	12.00 [304.8]	5-867472-1
	36.00 [914.4]	867472-3
	24.00 [609.6]	867472-2
	12.00 [304.8]	867472-1
REMARKS	"A" DIM	PART NO.

SCHEMATIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS CHK D.EABY 04-MAR-92 20-APR-92		 TE Connectivity			
DIMENSIONS: INCHES [mm]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME			
		0 PLC ± - 1 PLC ± - 2 PLC ± .03 [0.8] 3 PLC ± .015 [0.38] 4 PLC ± - ANGLES ± -		APVD D.EABY 20-APR-92 PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		RCPT ASSY 6 POSN WITH FLYING LEADS LGH	
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE TABLE		SEE TABLE		A2	00779	C-867472	—
CUSTOMER DRAWING						SCALE	4:1
						SHEET	1 of 1
						REV	F