

5100UE Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled



For more Information
please call

1-800-Belden1

**Description:**

14 AWG bare copper conductors, PP insulation, PVC jacket with ripcord, sequential footage marking every two feet.

Usage (Overall)**Suitable Applications:**

Intercom/PA Systems, Sound/Audio Systems, Fire Alarm (For color Red only)(Dual Rated)

Physical Characteristics (Overall)**Conductor****AWG:**

# Conductors	AWG	Stranding	Conductor Material
2	14	19x27	BC - Bare Copper

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (in.)
PP - Polypropylene	0.011

Outer Shield**Outer Shield Material:**

Outer Shield Material
Unshielded

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.017

Outer Jacket Ripcord:

Yes

Overall Cable**Overall Cabling Lay Length & Direction:**

Length (in.)	Twists (ft.)
4	3.0

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White

Overall Nominal Diameter:

0.226 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 37 lbs/1000 ft.

Max. Recommended Pulling Tension: 95 lbs.

Min. Bend Radius (Install)/Minor Axis: 2.250 in.

5100UE Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CL3R, FPLR
NEC Articles:	725 or 760
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1666 Vertical Riser
CSA Flame Test:	FT4

Plenum/Non-Plenum

Plenum Number:	6100UE
----------------	--------

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (μH/ft)
0.15

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
22.000

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
2.53

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
8 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5100UE 0021000	1,000 FT	36.000 LB	RED	C	2 #14 PP FRPVC
5100UE 008U1000	1,000 FT	34.000 LB	GRAY		2 #14 PP FRPVC
5100UE 0081000	1,000 FT	36.000 LB	GRAY	C	2 #14 PP FRPVC
5100UE 008500	500 FT	18.000 LB	GRAY	C	2 #14 PP FRPVC
5100UE 0101000	1,000 FT	36.000 LB	BLACK	C	2 #14 PP FRPVC

Notes:

C = CRATE REEL PUT-UP.

5100UE Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled

Revision Number: 3 Revision Date: 06-16-2008

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.