


ASSEMBLY- PUSHBUTTON SWITCH

CATALOG LISTING
3PB326-T 4

3PB326-T		REPLACES
PAGE 1 OF 1		
M	RELEASE NO. SR12211	
DRAWING NUMBER	27 OCT 98	
6	JAF	
ISSUE	CHECK	
REVISIONS		
A	CO19800	
M B F		
14 JAN 65		
B	SR12211	
RLD		
14 MAR 66		
C	OBS	
CO74434		
LJF		
29 APR 93		
D	RE-INST	
PR20855		
TSM		
21 OCT 93		
E	CO-	
93593		
P P F		
27 OCT 98		
DRAWN		
3 MARCH 64		
CHECK		
DAW		
3 MARCH 64		
CHECK		
MBF		



NOTES

- 1-UNIT INCLUDES CAT. LIST."ISM" TYPE BASIC SWITCH (3)
- 2-TERMINALS ARE PLATED FOR SOLDERING
- 3-SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
- 4-BASIC SWITCH HAS 24K SOLID GOLD CONTACTS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — 35 OZ APPROX
TOTAL TRAVEL — — — .100 APPROX
SWITCH NO. 1 AND 2
30 VOLTS DC RATING
INDUCTIVE — — — SEA LEVEL — — 1/2 AMP
50,000 FT — — 1/2 AMP
RESISTIVE — — — SEA LEVEL — — 1 AMP
50,000 FT — — 1 AMP
MAXIMUM INRUSH — — — — — 2 AMP

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T (3)
SWITCH NO. 3
250 VAC — — — — — 5 AMP
30 VOLTS DC RATING
INDUCTIVE — — — SEA LEVEL — — 3 AMP
50,000 FT — — 2.5 AMP
RESISTIVE — — — SEA LEVEL — — 5 AMP
50,000 FT — — 5 AMP
MAXIMUM INRUSH — — — — — 24 AMP

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[3PB326-T](#)