

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300390032](#)
Status: **Active**
Overview: [minichange_products](#)
Description: DeviceNet* Standard Cable Plus Drain, Micro-Change® to Mini-Change® Double Ended Cordset, 5 Poles, Straight Male-Internal Thread to Female-External Thread, Length 8.0m (26.25')

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E152210

General

Product Family Industrial Cordsets
Series [130039](#)
Connector End A Micro-Change® (M12)
Connector End B Mini-Change®
IP Rating IP67
Overview [minichange_products](#)
Product Name Micro-Change® (M12), Mini-Change®
Type Double Ended

Physical

Cable Diameter 6.86mm (.270")
Cable Length 8.0m (26.25')
Color - Cable Jacket Gray
Coupling Style Threaded
Gender Male-Female
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PVC
Material - Contact Copper
Material - Coupling Nut Die-Cast Zinc
Material - Plating Mating Gold
Orientation Straight
Poles 5
Temperature Range - Operating -20°C to +80°C
Wire Size AWG 22
Wire/Cable Type Shielded-Twisted Pair

Electrical

Current - Maximum per Contact 4A
Voltage - Maximum 250V AC/DC

Material Info

Old Part Number DND21A-M080

Reference - Drawing Numbers

Sales Drawing SD-130039-020



image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[130039Series](#)