

Product

Auto Transformer


Type No.

SAT 500

Technical Details

Safety Standards	VDE 0570, EN 61558-1 with EN 61558-2-13
Designated Voltage	Input: 230Vac
Designated Voltage	Output: 115Vac
Designated Current	Output: 4,34Aac
Designated Frequency	50-60Hz.
Protection Index	IP 20
Protection Class	I
Insulation Class	A (105°C)
Ambient Temperature	Max. 40°C
Short-Circuit Protection	Short-circuit-proof
Protection Device	Fuse-Link 5x20mm 4,0AT in output circuit
Input Connector	Approx. 2m flexible 3 core cable with a BS 1363 three pin plug
Output Connector	Approx. 1m flexible 3 core cable with USA 15A/125V three pin socket
Construction	Plastic enclosure
Weight	approx. 5,15Kg


Schematic Plan



Description

Short-circuit-proof auto transformer fully encapsulated in plastic enclosure.
Integrated fuse protection against short circuit and overload.
No isolation from mains.

Marking:



www.block-trafo.de

SAT 500

Autotransformer 500VA
Spartransformator 50-60Hz



VDE 0570/EN 61558 ta 40°C Cl.A IP 20



Input:

230V - 2,24A

Output:

115V - 4,34A — 4,0AT

⚠ This Transformer does not provide isolation from mains voltage ⚠
⚠ Der Transformator besitzt keine galvanische Trennung zum Netz ⚠

Approvals:

Dimensions

