



No hassle warranty

No waiting.

No shipping charges.



Our commitment to high-quality products and customer service is demonstrated by our industry exclusive "No Hassle" warranty. In the unlikely event that an Amprobe Test Tool requires warranty service, any of our local dealers are authorized to replace it, on the spot.

(note: \$500 MSLP limit)

TMD-55W Multilogger Thermometer with Wireless Download

Amprobe TMD-55W thermometer with wireless download capability is a professional choice for HVAC/R technicians, electricians, research, industrial process, and quality control. This model with dual inputs allows easy super-heat and sub-cool temperature measurement as well as cut-out and in temperature measurements.

Choose between models with 0.1% and 0.05% basic accuracy, single and triple displays or memory. Wireless communication is invaluable for applications requiring remote access to the instruments data.

- Backlit triple-display
- Built in memory
 - 16 sets, Maximum 1024 data points
- Data-logging:
 - 128 samples with real-time data per channel
- Easy Data Recall with up and down key: T1, T2, T1-T2, Time and Memory Location
- Thermocouple Offset Adjustment
- REC, MAX, MIN, MAX-MIN, Average, Relative Zero and HOLD functions
- Resolution 0.1°C/1°C, 0.1°F/1°F
- Warning beeper with Hi/Lo setting
- User selectable recording interval
- Real time clock with calendar



TMD-55W Multilogger Thermometer with Wireless Download

Data Sheet

General Specifications

Display	4½ digit liquid crystal display (LCD) with a maximum reading of 19999.
Polarity	Automatic, positive implied, negative polarity indication.
Low Battery Indication	The "⚡" is displayed when the battery voltage drops below the operating level.
Auto Power Off	30 minutes
Measurement Rate	2.5 times / second.
Operating Environment	0°C to 50°C (32°F to 122°F) <80% R.H.
Storage Environment	-20°C to 60°C (-4°F to 140°F) <70% R.H. with battery removed from meter.
Accuracy	Stated accuracy at 23°C ±5°C, <75% R.H.
Battery	1.5V x 4pcs AAA size
Battery Life	120 hours
Dimensions	L241.3 X W157.98 X H76.2mm (9.5 X 6.22 X 3 in)
Weight	Approx. 304g (0.67lb) including batteries and packaging box.

WIRELESS Features

Frequency Range	910~920MHz. Low current consumption less than 1mA. The transmitting distance can reach 25M without magnetic interference.
-----------------	---



TMD-55W Multilogger Thermometer with Wireless Download

Data Sheet

Electrical Specifications

Temperature Scale	User selectable Celcius or Fahrenheit
Measurement Range	Thermocouple Type Range
	K-TYPE (0.1°) : -200°C to 1372°C (-328°F to 2501°F)
	J-TYPE (0.1°): -210°C to 1200°C (-346°F to 2192°F)
	T-TYPE (0.1°): -200°C to 400°C (-328°F to 752°F)
	E-TYPE (0.1°): -210°C to 1000°C (-346°F to 1832°F)
	R-TYPE (1°): 0°C to 1767°C (32°F to 3212°F)
	S-TYPE (1°): 0°C to 1767°C (32°F to 3212°F)
	N-TYPE (0.1°): -50°C to 1300°C (-58°F to 2372°F)
Accuracy	K/J/T/E-TYPE
	±(0.05% rdg + 0.3°C) -50°C to 1372°C
	±(0.05% rdg + 0.7°C) -50°C to -210°C
	±(0.05% rdg + 0.6°F) -58°F to 2501°F
	±(0.05% rdg + 1.4°F) -58°F to -346°F
	N-TYPE
	±(0.05% rdg + 0.8°C) -50°C to 0°C
	±(0.05% rdg + 0.4°C) 0°C to 1300°C
	±(0.05% rdg + 1.6°F) -58°F to 32°F
	±(0.05% rdg + 0.8°F) 32°F to 2372°F
	R/S-TYPE
	±(0.05% rdg + 2°C) 0°C to 1767°C
	±(0.05% rdg + 4°F) 32°F to 3212°F



TMD-55W Multilogger Thermometer with Wireless Download

Data Sheet



Amprobe® Test Tools
website: www.Amprobe.com
email: info@amprobe.com
Everett, WA 98203
Tel: 877-AMPROBE

Amprobe® Test Tools
website: www.Amprobe.com
email: info@amprobe.com
Everett, WA 98203
Tel: 877-AMPROBE

©2010 Amprobe Test Tools. All rights reserved.
6/2010 TMD-55_DS Rev A