

# PRODUCT NUMBER


71600-YXXLF

LEAD FREE, SEE NOTE 6

TOTAL NB OF POSITION 04 TO 64  
SEE SHEET 2


OPTIONAL STRAIN RELIEF  
SEE SHEET 2

TRIANGLE INDICATES  
POSITION 1  
NOTE 5



## NOTES:

- 1 - PLASTIC MAT'L : GLASS FILLED HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: GREY
- 2 - PIN MATERIAL : PHOSPHOR BRONZE
- 3 - PRODUCT PACKAGED IN TUBES.
- 4 - TO DETERMINE DIMENSIONS :  
N = NUMBER OF POSITIONS PER ROW  
EXAMPLE : 8 POS N x 2.54 = 20.32mm
- 5 - 2x5, 2x6, 2x7 HAVE NO LEFT POLARIZING SLOT.  
- 2x2, 2x3 WITH CENTRAL KEY HAVE NO TRIANGLE, NO LEFT AND RIGHT POLARIZING SLOT.  
- 2x2 WITHOUT CENTRAL KEY HAS NO LEFT AND RIGHT POLARIZING SLOT.  
- 2x3, 2x4 WITHOUT CENTRAL KEY HAVE NO LEFT POLARIZING SLOT  
- 2x4 WITH CENTRAL KEY HAVE NO LEFT AND RIGHT POLARIZING SLOT
- 6 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS PER GS-22-008.  
PACKAGING SPECIFICATION AS PER GS-14-920.




|                          |          |     |          |                                       |                               |                  |                              |
|--------------------------|----------|-----|----------|---------------------------------------|-------------------------------|------------------|------------------------------|
| mat'l. code<br>SEE NOTES |          |     |          | surface<br>ISO 1302                   | tolerance<br>ISO 406 ISO 1101 | projection<br>mm | product family<br>2.54MM IDC |
| ltr                      | ecn no   | dr  | date     | tolerances unless otherwise specified |                               |                  | title                        |
| AP                       | F12-0046 | LMU | 12.04.25 | angles                                | X.X ±0.3                      |                  | QUICKIE III FEM              |
| AR                       | B-17851  | LMU | 14.06.05 | linear                                | X.XX ±0.13                    |                  | 0.76µm Au                    |
|                          |          |     |          |                                       | X.XXX ±0.05                   | scale 5:1        |                              |
| AK                       | F05-0180 | LMU | 05.04.22 | dr                                    | D.LE                          | 01.01.24         | dwg no                       |
| AL                       | F06-0270 | LMU | 06.09.12 | engr                                  | P.NZ                          | 01.01.24         | sheet 1 of 2                 |
| AM                       | F06-0274 | LMU | 06.09.25 | chr                                   | JF.N                          | 01.01.24         | size                         |
| AN                       | F09-0233 | LMU | 09.12.15 | appd                                  | P.NZ                          | 01.01.24         | A3                           |
| sheet                    | revision | AR  | AF       |                                       |                               |                  | type                         |
| index                    | sheet    | 1   | 2        |                                       |                               |                  | CUSTOMER Drawing             |




Copyright FCI

| STRAIN RELIEF OPTION AVAILABILITY                                         | Nbr OF POSITIONS |
|---------------------------------------------------------------------------|------------------|
| 1/6                                                                       | 04               |
| 0/1/2/3/6                                                                 | 06               |
| 0/1/2/3/6                                                                 | 08               |
| 0/1/2/3/6                                                                 | 10               |
| 0/1/2/3/6                                                                 | 14               |
| 0/1/2/3/6                                                                 | 16               |
| 0/1/2/3/6                                                                 | 18               |
| 0/1/2/3/6                                                                 | 20               |
| 0/1/3                                                                     | 24               |
| 0/1/2/3/6                                                                 | 26               |
| 0/1/2/3/6                                                                 | 30               |
| 0/1/2/3/6                                                                 | 34               |
| 0/1/2/3/6                                                                 | 40               |
| 0/1/2/3/6                                                                 | 50               |
| 0/1/2/3/6                                                                 | 60               |
| 0/1/2/3/6                                                                 | 64               |
| PLATING<br>0.76µm GOLD ON CONTACT AREA<br>1.27 µm Ni REMAINDER OF PRODUCT |                  |


|                      |
|----------------------|
| 624                  |
| 304                  |
| 204 / 224            |
| 004                  |
| DASHES NOT AVAILABLE |




LOW PROFILE  
STRAIN RELIEF




STANDARD  
STRAIN RELIEF




LATCHING STRAIN RELIEF  
FOR SLIM HEADER




WITHOUT STRAIN RELIEF



WITH LOW PROFILE STRAIN RELIEF



WITH STANDARD STRAIN RELIEF



WITH LATCHING STRAIN RELIEF

|                |             |         |               |         |             |          |
|----------------|-------------|---------|---------------|---------|-------------|----------|
| 71600-6YYLF    | ●           |         |               |         |             | ●        |
| 71600-3YYLF    |             | ●       | ●             |         |             |          |
| 71600-2YYLF    | ●           |         |               |         | ●           |          |
| 71600-1YYLF    | ●           |         |               |         | ●           |          |
| 71600-0YYLF    | ●           |         | ●             |         |             |          |
| PRODUCT NUMBER | WITH        | WITHOUT | STANDARD      | WITHOUT | LOW PROFILE | LATCHING |
|                | CENTRAL KEY |         | STRAIN RELIEF |         |             |          |

|             |          |     |          |                                       |                  |            |                   |
|-------------|----------|-----|----------|---------------------------------------|------------------|------------|-------------------|
| mat'l. code |          |     |          | surface                               | tolerance        | projection | product family    |
| ltr         | ecn no   | dr  | date     | ISO 1302                              | ISO 406 ISO 1101 | ISO 1101   | QUICKIE           |
| AF          | B-17851  | LMU | 14.06.05 | tolerances unless otherwise specified |                  | mm         | title             |
|             |          |     |          | angles                                | linear           | scale N/A  | IDC RECEPT DR     |
| AA          | F10199   | GCO | 01.04.26 |                                       |                  |            | dwg no            |
| AB          | F03019   | DLE | 03.01.23 | dr                                    | D.LE             | 01.01.24   | sheet 2 of - size |
| AC          | F05-0180 | LMU | 05.04.22 | engr                                  | P.NZ             | 01.01.24   | A3                |
| AD          | F06-0270 | LMU | 06.09.12 | chr                                   | JF.N             | 01.01.24   |                   |
| AE          | F06-0274 | LMU | 06.09.25 | appd                                  | P.NZ             | 01.01.24   |                   |
| sheet       | revision |     |          |                                       |                  |            | type              |
| index       | sheet    |     |          |                                       |                  |            | CUSTOMER Drawing  |