


REV.	DATE	DESCRIPTION
NC	01/08/97	INITIAL RELEASE
A	06/10/07	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex									
8						DRAWN	G.R.S.	06/10/07											
7						CHECKED				PART DESCRIPTION SMA FEMALE TO N FEMALE ADAPTER —									
6						ISSUED													
5						SHEET	1 OF 1				PART NO. 242115								
4					CAD FILE														
3	CONTACT PIN	PHOS. BRONZE	GOLD	1	C:/242/242115.DWG					DWG. NO.		242115.DWG		REV.	A	SIZE	A	SCALE	NA
2	INSULATOR	TEFLON	NATURAL	1	DO NOT SCALE DRAWING														
1	BODY	BRASS	NICKEL	1															
	DESCRIPTION	MATERIAL	FINISH	QTY															