





UPDATE TITLE BLOCK EC NO: UCP2006-0080 DRAWN: LOWE CHKCD: 2005/07/20 APPR: FSW TH 2005/07/21	DESCRIPTION QUALITY SYMBOLS ▼=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY KBW	DATE 3/1/89	TITLE .093/(2.36) HOUSINGS PLUG AND RECEPTACLE 12 CKT, .198/(5.03)CTR.			
		4 PLACES ± --- ± ---	3 PLACES ± --- ± .010	CHECKED BY RW	DATE 3/1/89					
		2 PLACES ± 0.25 ± .014	1 PLACE ± 0.35 ± ---	APPROVED BY RAS	DATE 3/1/89	MOLEX INCORPORATED				
		ANGULAR ± 2 °		MATERIAL NO.					DOCUMENT NO.	
AE1	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-1360-*				
				SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

13 12 11 10 9 8 7 6 5 4 3 2 1

PLUG

ORDER NO	ENG NO
03-09-2 I21	I360-P
03-09-2 I22 	I360-PI
03-09-7 I21	I360-PBK
03-09-7 I22 	I360-PIBK
OBSOLETE	

RECEPTACLE

ORDER NO	ENG NO
03-09-1 I21	I360-R
03-09-1 I22	I360-RI
03-09-1 I25	I360-R2
03-09-1 I26	I360-R3
03-09-6 I21	I360-RBK
03-09-6 I22	I360-RIBK
03-09-6 I25	I360-R2BK
03-09-6 I26	I360-R3BK
03-09-6 I23	I360-RIRD
03-09-6 I24	I360-RIYW

LEGEND: PLUG

I360-P***

P = PLUG

BLANK = WITHOUT EARS

I = WITH MOUNTING EARS

COLOR: _____

BLANK = NATURAL COLOR

AM = AMBER BK = BLACK BU = BLUE

BN = BROWN GY = GRAY GN = GREEN

OR = ORANGE RD = RED YW = YELLOW

LEGEND: RECEPTACLE

I360-R***

R = RECEPTACLE

BLANK = WITH PREBENT EARS ONLY

1 = WITHOUT EARS/WITHOUT LOCKING RAMPS

2 = WITH PREBENT EARS & LOCKING RAMPS

3 = WITH LOCKING RAMPS ONLY


COLOR: _____

BLANK = NATURAL COLOR

AM = AMBER BK = BLACK BU = BLUE

BN = BROWN GY = GRAY GN = GREEN

OR = ORANGE RD = RED YW = YELLOW






RECOMMENDED PANEL OPENING


HOUSING	DIM. *A*	DIM. *B*	*C* PREBENT EAR	*C* STANDARD EAR
PLUG	1.155/(29.34)	.760/(19.30)	.40/(10.2)	.36/(9.1)
RECEPT.	1.050/(26.67)	.725/(18.42)	.41/(10.4)	.37/(9.4)

DETAIL A



.093/(2.36) STANDARD MOUNTING EAR
(SCALE 4:1)

DETAIL B



.093/(2.36) PREBENT MOUNTING EAR
(SCALE 4:1)

NOTES:

1. MATERIAL: NYLON TYPE 6/6, UL94V-2

2. FINISH: N/A

3. PRODUCT SPECIFICATION: PS-02-09, PS-43660-9999

4. PACKAGING SPECIFICATION: PK-1360-001

 CIRCUIT I.D. NUMBERS ON SIDE OF HOUSING APPEAR ON PARTS FROM TOOLS BUILT AFTER 10/22/91

 WHERE DENOTED IN CHART, TOOLS ARE BUILT WITH PREBENT MOUNTING EARS PER DETAIL B AND SUPERSEDE ALL TOOLS PREVIOUSLY BUILT WITH THE STANDARD EARS.

UPDATE TITLE BLOCK

EC NO: UCP2006-0080

DRWN: JLOWE

CHKD: _____

APPR: FSN TH

REV AE1

2005/07/20

2005/07/20

2005/07/21

QUALITY SYMBOLS

=0

=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± .010
2 PLACES	± 0.25	± .014
1 PLACE	± 0.35	± ---

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

IN/MM

DRAWN BY KBW

CHECKED BY RW

APPROVED BY RAS

MATERIAL NO.

SIZE C

SCALE

2:1

DESIGN UNITS

INCH

THIRD ANGLE PROJECTION

TITLE

.093/(2.36) HOUSINGS
PLUG AND RECEPTACLE
12 CKT, .198/(5.03) CTR.

MOLEX INCORPORATED

SD-1360-*

SHEET NO.

2 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

ib_frame_C_P_ME_T
Rev. D 2004/04/02

12 11 10 9 8 7 6 5 4 3 2 1