






DIMENSIONS: mm (in.)**Mechanical Specifications:**

- Timing: Non Shorting
- Type: DPDT
- Operating Force: 250gf±100gf
- Life Test: 10,000 Cycles 15~18 Cycles/Min.

Electrical Specifications:

- Rating: 0.5A / 50V DC
- Contact Resistance: 30mΩ
- Insulation Resistance: 100MΩ
- Dielectric Strength: 500VAC 1 Min.

Note:

- RoHS Compliant

Slide Switch
103-22037-EV

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-22037-EV](#)