



F1238-S series



Size: (119 x 119 x 38 mm)

4.69 x 4.69 x 1.5 inches

- Broad range of models to meet air flow and sound noise targets
- Electronic locked rotor sensor, auto-restart, reverse polarity protection
- 5, 12, 24 or 48 VDC
- Lead wires or terminal version; reinforced flanged frame; ball bearings
- Options include tachometer or locked rotor output signal



Model No.	Rated Voltage V	Current mA	5	12	24	48	Revolution RPM	Air Volume CFM	Maximum Static Pressure (in H ₂ O)	Sound Noise dBA	Weight oz
F1238S-S	5/12/24/48	520 180 90 60					1,800	83	0.14	34	8.58
F1238L-S	5/12/24/48	800 290 145 80					2,050	94	0.17	36	8.58
F1238M-S	12/24/48	- 360 180 120					2,300	105	0.21	38	8.58
F1238H-S	12/24/48	- 440 220 140					2,500	115	0.25	41	8.58
F1238E-S	12/24/48	- 700 350 210					2,800	126	0.28	43	8.58
F1238X-S	12/24	- 950 500 -					3,100	140	0.30	45	8.58

* Available with quick disconnect terminal block.