




# SMA

## Panel Jack Receptacles – 4-hole Flange

Amphenol®

|                                                                                                                                                                                                                                                                              |                                                                                                                                                                                                                                                    |                                                                                                                                                                                                                                                                                                                               |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <p>Fig. 1</p>  <p>SMA Panel Jack Receptacle<br/>4-Hole Square Flange Mount<br/>Solder Cup Terminal<br/><b>901-9215</b><br/>Gold Plated Body<br/><b>901-9215-SF</b><br/>Passivated Body</p> | <p>Fig. 2</p>  <p>SMA Panel Jack Receptacle<br/>4-Hole Square Flange Mount<br/>Post Terminal<br/>Flush TFE<br/>Countersink Flange Holes<br/><b>901-9758</b></p> | <p>Fig. 3</p>  <p>SMA Panel Jack Receptacle<br/>4-Hole Square Flange Mount<br/>Slot Terminal<br/><b>901-9204-4CC</b><br/>Gold Plated Body<br/><b>901-9204-4CCSF</b><br/>Passivated Body<br/><b>901-9204-3CCSF</b><br/>Passivated Body</p> |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

### SMA PANEL JACK RECEPTACLES – 4-hole square flange mount

| Terminal Type                | Dimensions In. (mm) |           | Plt. | Ins. | Notes                            | Amphenol Number       | Fig. |
|------------------------------|---------------------|-----------|------|------|----------------------------------|-----------------------|------|
|                              | a                   | c         |      |      |                                  |                       |      |
| Solder Cup .200"(5.1mm) Long | .575(14.6)          | .375(9.5) | P10  | D1   | Captive Contact, Gold Plt. Body  | <b>901-9215</b>       | 1    |
|                              | .575(14.6)          | .375(9.5) | P13  | D1   | Captive Contact, Passivated Body | <b>901-9215-SF</b>    | 1    |
| Slot .015"(0.4mm) Wide       | .425(10.8)          | .375(9.5) | P9   | D1   | Captive Contact, Gold Plt. Body  | <b>901-9204-4CC</b>   | 3    |
|                              | .425(10.8)          | .375(9.5) | P12  | D1   | Captive Contact, Passivated Body | <b>901-9204-4CCSF</b> | 3    |
| Slot .030"(0.8mm) Wide       | .425(10.8)          | .375(9.5) | P12  | D1   | Captive Contact, Passivated Body | <b>901-9204-3CCSF</b> | 3    |
| Blunt Post .115"(2.9mm) Long | .490(12.4)          | .375(9.5) | P13  | D1   | Captive Contact, Passivated Body | <b>901-9758</b>       | 2    |