



CH31 Series Single Row Board Mount Pin Header

2.54mm(.100") Center spacing

©Mates with CB33, CB37 and CB39



RoHS Compliant

E159616




$$A = 2.54 \times \text{No. of Spaces}$$


$$B = A + 2.36$$



Option Code	Pin Dimension	
	C	D
00	6.0(.236)	3.00(.118)
01	6.26(.246)	3.00(.118)
02	5.86(.231)	3.00(.118)
03	8.86(.349)	3.00(.118)





Recommended P.C. Board Layout



$$A = 2.54 \times \text{No. of Spaces}$$

$$B = A + 2.36$$



Option Code	Pin Dimension	
	C	D
00	6.0(.236)	3.00(.118)
01	6.26(.246)	3.00(.118)
02	5.86(.231)	3.00(.118)
03	8.30(.327)	3.00(.118)
04	7.26(.286)	3.00(.118)

Ordering Code

1
CH 3 1

2
4 0

3
2

4
V

5
1

6
0 0

- 1** Series No.
- 2** Circuits:
02 to 40
- 3** Plating code:
2= Gold flash over Nickel plated
*Optional plating available but MOQ requested
- 4** Tail Style:
V= Straight DIP Type
H= Right Angle DIP Type
- 5** Insulator Color:
1= PBT UL 94V-0, Color Black
2= PBT UL 94V-0, Color Black (RoHS Compliant)
- 6** Other options:
00= Standard
*Special options Consult manufacturer