


19" Punchdown Rack Mount Panels

- Accept punchdown bases for rack mount applications



P110B100R2BY



P110B100R4BY

Part Number	Part Description	No. of Rack Spaces^	Std. Pkg. Qty.	Std. Ctn. Qty.
P110B100R2BY	Panel accepts up to 2 RU of punchdown bases.	2	1	10
P110B100R4BY	Panel accepts up to 4 RU of punchdown bases.	4	1	10


^One rack space = 1.75" (44.45mm).
Includes mounting screws.

Pan-Punch® Category 5e 19" Rack Mount Panels

- Exceed ANSI/TIA-568-C.2 Category 5e standard
- Mount to standard TIA/EIA 19" racks
- Ideal for use in cross-connects and consolidation point applications
- Exclusive deeper channel to facilitate TIA/EIA Category 5e cabling installations



P110B100R2Y



P110B100R4WJY

Part Number	Part Description	No. of Rack Spaces^	Std. Pkg. Qty.	Std. Ctn. Qty.
P110B100R2Y	Two 100-pair bases pre-mounted to panel.	2	1	10
P110B100R4WJY	Two 100-pair bases with jumper troughs pre-mounted to panel.	4	1	10

^One rack space = 1.75" (44.45mm).
Includes mounting screws.
Termination tool available on page B.87 of SA-NCCB51.
For connecting blocks see page B.84 of SA-NCCB51.
Can be clearly identified with label holders and recommended labels shown on page B.80 of SA-NCCB51.