

THB.385.A1A

TeePlug panel mount 3 pole Screw terminal, 4 mm max conductor size IP66-68 17A 400V 1 cable entry



PRODUCT SPECIFICATIONS

Temperature "T" rating	T85
Minimum cable diameter (mm)	7
Maximum cable diameter (mm)	12
Fixing system	Panel mount
Cable entries	1
Number of poles	3
Terminal type	Screw
Body material	PA66
Max conductor size (Sq mm)	4
Max current (A)	17
Max voltage (V)	400
Minimum temp rating °C	-40
Max temp rating °C	125
IP rating	66-68 (From front when mounted with relevant connector)