

MICRO SWITCH

FREEPORT ILLINOIS, U. S. A

A DIVISION OF HONEYWELL INC.

FED. MFG. CODE 91929

ACTUATOR SWITCH

CATALOG LISTING

8AS228**8AS228**

PAGE 1 OF 1

MDRAWING
NUMBER☒ISSUE
4

REPLACES

RELEASE NO. PR-14860

CHECK

REVISIONS

A C074852

JD B

24 MAY 93

B 201512

DLT

02 NOV 00

C 0006685

KSR

19 JUL 04

19 JUL 04

AK

CHECK



30 JUN 86

KAG

CHECK


27 JUN 86

DRAWN

RASTER
FO-52848-B2-56 UNC X .625 REF ROUND HEAD MACHINE SCREW
(PART NO. JS-10365) (2)2-56 UNC HEX NUT
(PART NO. JS-10119) (2)LOCKWASHER
(PART NO. JS-10120) (2).19 DIA X .19 WIDE CORROSION RESISTANT STEEL ROLLER
(CONCENTRICITY .005 FIM)**NOTES**1 - UNIT INCLUDES CATALOG LISTING "ISE226" BASIC
AND "JE-17" ACTUATOR FURNISHED UNASSEMBLED2 WIRE LEADS PER MIL-W-22759/7, MARKED WITH CIRCUIT
IDENTIFICATION AND WIRE GAGE (1-20, 2-20, ETC...) PER MIL-W-5088

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**

OPERATING FORCE --- 12 OZ MAX

RELEASE FORCE ---- 2 OZ MIN

DIFFERENTIAL TRAVEL — .025 MAX

OVERTRAVEL ----- .015 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

S P N C

SCALE FULL

DO NOT
SCALE PRINTUNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) ± .030

TWO PLACE (.00) ± .015

THREE PLACE (.000) ± .005

ANGLES ±

RAW MATERIAL - COMMERCIAL STANDARD

DIMENSIONS ARE IN INCHES AND ARE
TO BE MET BEFORE PROTECTIVE
COATINGS ARE APPLIED

MICRO SWITCH STANDARDS APPLY

WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[8AS228](#)