

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1203410301

Status:

Active

Overview:

Brad Industrial Ethernet Solutions

Description:

Micro-Change M12 CAT6A Double-Ended Cordset, 8 Poles, Male (Straight) to Male (Straight), 26 AWG, Shielded PUR Cable, 1.0m (3.28') Length



Documents:	
Drawing (PDF)	Packaging Specification PK-120341-300 (PDF)
Product Specification PS-120341-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Cordsets
Series	120341
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Industrial Ethernet Solutions
Performance Category	6A
Product Name	Micro-Change (M12) Cat6A
Protocol	N/A
Region	America, Asia, Europe
Type	Double Ended
UPC	884982411869
Physical	
Cable Diameter	6.40mm (.252")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Blue
Coupling Style	Threaded
Gender	Male-Male
Keyway	X-coded
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	88.951/g
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-40°C to +70°C
Wire Size AWG	26
Wire/Cable Type	Shielded PUR
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	48V
Material Info	
Engineering Number	E22E06020M010
Reference - Drawing Numbers	
Packaging Specification	PK-120341-300
Product Specification	PS-120341-001-001
Sales Drawing	1203410300-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2020)4578-DC (25 June 2020)	
Lead	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120341 Series

Mates With

120341 Micro-Change CAT6A Receptacles

This document was generated on 07/24/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION