

3M™ Pak 50 Low Profile Wiremount Socket

.050" for .025" Pitch Cable

P25LE Series



- P25LE terminates 25 mil pitch, 30 AWG stranded wire, PVC insulated, flat ribbon cable
- Low profile 11.8 mm mated height
- P50LE mate offers surface mount, straight and right angle thru-hole options
- Latch/eject mechanism maintains a secure connection
- Cable strain relief standard
- Tooling available for customer cable assembly termination
- RoHS Compliant. See the Regulatory Information Appendix (RIA) in the "RoHS Compliance" section of www.3Mconnector.com for compliance information (RIA E1 and C1 apply)

Date Modified: February 17, 2010

TS-1142-B
Sheet 1 of 2

Physical

Insulator:

Material: Glass Filled Nylon

Flammability: UL 94V-0

Color: Brown

Contact Material: Phosphor Bronze

Plating:

Underplating: Nickel

Wiping Area: Gold Flash

Termination Area: Gold Flash

Wire Accommodation: 30 AWG Stranded PVC Flat Ribbon Cable (3M #3754 or approved equivalent)

Mating Compatibility: TS-1148

Electrical

Current Rating: 0.5 A

Insulation Resistance: $> 1 \times 10^9 \Omega$ at 250 V_{DC}

Withstanding Voltage: 300 V_{AC} for 1 minute

Environmental

Temperature Rating: -55°C to +85°C

UL File No.: E68080


3M™ Pak 50 Low Profile Wiremount Socket

.050" for .025" Pitch Cable

P25LE Series

Product Table / Dimensions

Contact Quantity	A	B	C	D	E	F	Contact Quantity	A	B	C	D	E	F
20	29.63 [1.167]	18.23 [0.718]	17.83 [0.702]	17.03 [0.670]	13.43 [0.529]	11.43 [0.450]	60	55.03 [2.167]	43.63 [1.718]	43.23 [1.702]	42.43 [1.670]	38.83 [1.529]	36.83 [1.450]
30	35.98 [1.417]	24.58 [0.968]	24.18 [0.952]	23.38 [0.920]	19.78 [0.779]	17.78 [0.700]	68	60.11 [2.367]	48.71 [1.918]	48.31 [1.902]	47.51 [1.870]	43.91 [1.729]	41.91 [1.650]
40	42.33 [1.667]	30.93 [1.218]	30.53 [1.202]	29.73 [1.170]	26.13 [1.029]	24.13 [0.950]	80	67.73 [2.667]	56.33 [2.218]	55.93 [2.202]	55.13 [2.170]	51.53 [2.029]	49.53 [1.950]
50	48.68 [1.917]	37.28 [1.468]	36.88 [1.452]	36.08 [1.420]	32.48 [1.279]	30.48 [1.200]	100	80.43 [3.167]	69.03 [2.718]	68.63 [2.702]	67.83 [2.670]	64.23 [2.529]	62.23 [2.450]



mm [Inch]	
Tolerance Unless Noted	
0.0	0.00
mm	± .1 ± .10

() Dimensions used for Reference Only

Note: Strain relief standard.

Conn Size	Locator Plate PN
20	3443-127A
40	3443-127B
30 & 50	3443-127C
60	3443-127D
68	3443-127E
80 & 100	3443-127F

Ordering Information

P25LE - XXXS - DA (RIA E1 and C1 apply)

Contact Quantity: _____
See Table

TS-1142-B
Sheet 2 of 2



Electronic Solutions Division
Interconnect Solutions
<http://www.3Mconnector.com>

3M is a trademark of 3M Company.
For technical, sales or ordering information call
800-225-5373

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



3M Electronics Solutions Division

6801 River Place Blvd.
Austin, TX 78726-9000
U.S.A.
1-800-225-5373
www.3Mconnector.com

Please recycle. Printed in USA.
© 3M 2010. All rights reserved.
RIA-2217B-E

3M is a trademark of 3M Company.