


Miscellaneous Audible Signal Devices (continued)


Electronic DC Buzzers

Part Number	Rated Voltage (VDC)	Operating Voltage (VDC)	Max Current (mA)	Sound Output	Terminal Type	Frequency	Operating Temperature
BS2316L-01	1.5	1.3 - 2	25 mA	75 @ 30cm dB	2 Leadwires	400 ± 50Hz	-40° to +70°C
BS2316L-03	3	2 - 5	25 mA	75 @ 30cm dB	2 Leadwires	400 ± 50Hz	-40° to +70°C
BS2316L-06	6	4 - 9	25 mA	75 @ 30cm dB	2 Leadwires	400 ± 50Hz	-40° to +70°C
BS2316L-09	9	6 - 15	25 mA	75 @ 30cm dB	2 Leadwires	400 ± 50Hz	-40° to +70°C
BS2316L-12	12	9 - 20	25 mA	75 @ 30cm dB	2 Leadwires	400 ± 50Hz	-40° to +70°C
BS2316L-24	24	10 - 27	25 mA	75 @ 30cm dB	2 Leadwires	400 ± 50Hz	-40° to +70°C
BS2316P-06-C	6	4 - 8	35 mA	80 @ 30cm dB	4 Pins	400 ± 50Hz	-40° to +70°C
BS2316P-09-C	9	6 - 12	35 mA	80 @ 30cm dB	4 Pins	400 ± 50Hz	-40° to +70°C
BS2316P-12-C	12	8 - 16	35 mA	80 @ 30cm dB	4 Pins	400 ± 50Hz	-40° to +70°C
BS2316P-24-C	24	16 - 27	35 mA	80 @ 30cm dB	4 Pins	400 ± 50Hz	-40° to +70°C
BS2620FV-03	3	2 - 4	70 mA	75 @ 100cm dB	2 Fast-on	400 ± 50Hz	-40° to +70°C
BS2620FV-06	6	4 - 8	70 mA	75 @ 100cm dB	2 Fast-on	400 ± 50Hz	-40° to +70°C
BS2620FV-12	12	8 - 16	60 mA	75 @ 100cm dB	2 Fast-on	400 ± 50Hz	-40° to +70°C
BS2620FV-24	24	20 - 28	60 mA	75 @ 100cm dB	2 Fast-on	400 ± 50Hz	-40° to +70°C
BS2620PH-03-C	3	2 - 4	30 mA	75 @ 100cm dB	4 Pins	400 ± 50Hz	-40° to +70°C
BS2620PH-06-C	6	4 - 8	30 mA	75 @ 100cm dB	4 Pins	400 ± 50Hz	-40° to +70°C
BS2620PH-12-C	12	8 - 16	20 mA	75 @ 100cm dB	4 Pins	400 ± 50Hz	-40° to +70°C
BS2620PH-24-C	24	20 - 28	20 mA	75 @ 100cm dB	4 Pins	400 ± 50Hz	-40° to +70°C
BR2818L-01	1.5	1.3 - 2	35 mA	80 @ 30cm dB	2 Leadwires	400 ± 50Hz	-40° to +70°C
BR2818L-03	3	2 - 5	35 mA	80 @ 30cm dB	2 Leadwires	400 ± 50Hz	-40° to +70°C
BR2818L-06	6	4 - 9	35 mA	80 @ 30cm dB	2 Leadwires	400 ± 50Hz	-40° to +70°C
BR2818L-09	9	6 - 15	35 mA	80 @ 30cm dB	2 Leadwires	400 ± 50Hz	-40° to +70°C
BR2818L-12	12	9 - 20	35 mA	80 @ 30cm dB	2 Leadwires	400 ± 50Hz	-40° to +70°C
BR2818L-24	24	20 - 28	35 mA	85 @ 30cm dB	2 Leadwires	400 ± 50Hz	-40° to +70°C
BR2818L-48	48	30 - 54	35 mA	85 @ 30cm dB	2 Leadwires	400 ± 50Hz	-40° to +70°C


BS2316 Series



BS2620FV Series



BS2620PH Series



BR2818 Series

