



NOTES:

- 1 MAXIMUM RECOMMENDED STROKE .500
- 2 FOR USE WITH THE 206-375 TOOL. FOR OTHER TOOLS AND/OR STROKE COMBINATIONS, REFER TO THE STROKE LIMITER CHART (HK1122) OR CONSULT AN AFS/HUCK SPECIALIST.
- 3 SHIP WITH: STOP 126747, DEFLECTOR 126748-2 AND (2) .030 SHIMS 128290 REFERENCE PB563 FOR PROPER USE.
- 4 128621C ASSEMBLY CONSISTS OF 128511C COLLET AND 128487 DRAWBAR.

REV	DESCRIPTION	DET	DATE
C	REWROTE NOTES: ADDED .453 CENTER TO EDGE DIMENSION	MK	11/19/09
D	128511C WAS 128621C. ADDED 128487	JJC	08/01/12

(D)	128487	1	DRAWBAR	9
	126748-2	1	UNITIZED DEFLECTOR	8
(D)	128511C	1	COLLET	7
	126745	1	GUARD	6
	120095	1	DEFLECTOR	5
	122727	1	BARBED RETAINER	4
	122725	1	UNITIZED CHUCK JAW	3
	127582-1	1	TOP GUARD	2
	127073C	1	ANVIL	1
	PART NO.	QTY	DESCRIPTION	ITEM

IDENTIFICATION PER SPEC 42-311: ★ ETCH			
ITAR:		HUCK INTERNATIONAL, INC., I.S.D. 1 CORPORATE DR, P.O. BOX 2270 KINGSTON, NEW YORK 12401	
ECCN: EAR99		CLEARANCE NOSE ASSEMBLY -08 GP STRADDLE NOSE	
SCH B#: 8467.99.0190		DET: MVM	CK: DATE: 10/19/04 SCALE: 2:1
HTS: 8467.99.0190		B	99-3740C