


Date	Rev.	Description



Tolerance Unless Otherwise Specified			
0	>	mm ±	ANGLE
>		mm ±	0° > ° REF ±
>		mm ±	° > ° ±
>		mm ±	° > ° ±

- NOTE :
1. MAXIMUM ELECTRIC CURRENT :

A.W.G.	22	20	18	16
AMP.	9	12	17	18
 2. MAXIMUM ELECTRICAL RATING : Δ 105°C 600 VOLTS MAX.
 3. INSULATION MATERIAL : VINYL
 4. INSULATION COLOR : RED
 5. TERMINAL MATERIAL : COPPER
 6. WIRE RANGE : 22-16 A.W.G. (0.5-1.5 mm²)
 7. TERMINAL SURFACE TREATMENT : TIN PLATED
 8. TERMINAL THICKNESS : 0.75 mm

DCC. NO.
A4 DRAWING NO.

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.			
		JAMECO NO.	GOLDSUN NO.		
		103684	RVS1-3.7		
DRAWN: Kiki Chen		Description			Rev.
VERIFY PEOPLE: Ada Zheng , Ivy Lan		SOLDERLESS TERMINALS			1
		UNIT:	SCALE:	SHEET 1 OF 1	CAS No:
		mm			ERN No: