


SR20A 200W SOLDERING IRON



DATA SHEET


769-3157



Iron featured without bit

SPECIFICATIONS SR20A (ANGLED) 200WATT SOLDERING IRON

NOMINAL POWER (W)	200
STANDARD VOLTAGE	230
NOMINAL TIP TEMP (°C)	430
FITTED BIT (D.F.)	¾" (19mm)
CABLE LENGTH (m)	2.0
CABLE TYPE	Rubber with European plug
HANDLE MATERIAL	Wood
COUNTRY OF ORIGIN	U.K.
WEIGHT gms. (approx.)	950
DIMENSIONS (approx.)	A: (bit) 55mm. B: 230mm. C: 90mm. D: 325mm.



TYPICAL APPLICATIONS:

General soldering on transformer casings, soldering on commutators up to 2" dia. tin plate & metal box fabrications.