


MT SERIES

RELAY SOCKETS



CUSTOM CONNECTOR

DESCRIPTION

8 and 14 Pin Miniature Sockets, DIN Rail Mountable

ELECTRICAL RATING

• 300 Volts, 10 Amps***NEW UPGRADED RATING***

CONSTRUCTION

- Contacts** • Brass, Nickel Plated
- Screws** • M3 x .5 x 6.5 mm Steel, Zinc Plated, Wire Range #14 - #22 Solid or Stranded
- Molding** • Break Resistant Thermoplastic Black Standard, Grey Available

AGENCY APPROVALS

- UL recognized, File No. E60008
- CSA certified, File No. LR29513
- CE



ORDERING CODE

PART NO.

MT08-PC
MT14-PC

DESCRIPTION

DPDT, 8 Pin Miniature
4PDT, 14 Pin Miniature

TERMINAL TYPE

Pressure Clamp Screws
Pressure Clamp Screws


ACCESSORIES

PART NO.

C-103-PM
C-104-PM
C-105-PM
C-106-2PM
C-108-PM
C-108-2PM
HDB-4

DESCRIPTION (Refer to the accessories pages 25-27)

Prepunched Aluminum DIN Rail (1 Meter Lengths)
Prepunched Steel DIN Rail (1 Meter Lengths)
Prepunched Steel DIN Rail (1 Meter Lengths)
Prepunched Steel DIN Rail (2 Meter Lengths)
Prepunched Raised Aluminum DIN Rail (1 Meter Lengths)
Prepunched Raised Aluminum DIN Rail (2 Meter Lengths)
Hold Down Spring



MT SERIES NOTE:

MT08-PC is the same as MT14-PC but with terminals 2,3,6,7,10 and 11 omitted