

RACPRO1-4SP/24V/10A Cut Sheet



RECOM Power RACPRO1 series electronic circuit protector, current-limiting, adjustable 3.5–11.5 A, 24 VDC, 4 independent channel(s), 35 mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RACPRO1-4SP/24V/10A>

Technical Specifications

Brand	RECOM Power
Item	Circuit protector
Series	RACPRO1
Circuit Breaker Type	Compact
Circuit Type	Supplementary
Current-Limiting	Yes
Amperage Rating	Adjustable 3.5–11.5 A
Input voltage range	22–28 VDC
Output Voltage Range	22–28 VDC

Channels	4 independent
Trip Type	Electronic
Reset	Remote or local
UL Rating	UL 61010 and UL 62368
NEC Class 2	No
HACR Rated	No
Reverse Feed Capable	No
Mounting	35 mm DIN rail
Connection	Push-in cage clamp

Agency Approvals

UL Listed File #	None
UL Recognized File #	QQJQ2.E224736
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/RACPRO1-4SP_24V_10A.pdf
See store item page for other formats.