




MISCELLANEOUS



Utility Compartment Box




- 10"x4.75"x1.5" (LxWxH)
- Up to 12 compartment
- Removable partitions




Description	Part No.
Utility Compartment Box	900-039

Utility Component Storage Box




- 8.25"x4.7"x1.25" (LxWxH)
- Material: P.P.




Description	Part No.
Utility Component Storage Box	902-112

Utility Compartment Box




- 11"x7"x1.75" (LxWxH)
- Removable partitions
- 15 pcs dividers included



Description	Part No.
Utility Compartment Box	900-040


Utility Compartment Box



- 6.5"x3.75"x1.75" (LxWxH)
- 5 compartments on one side, 8 on the other
- Lid opens on both sides doubling the number of items to be stored

Description	Part No.
Utility Compartment Box	900-043

Utility Compartment Box




- 8"x5.25"x1.5" (LxWxH)
- Removable partitions
- 12 pcs dividers included



Description	Part No.
Utility Compartment Box	900-041

Utility Component Storage Box




- 3"x3-3/16"x13/16" (LxWxH)
- Material: P.P.




Description	Part No.
Utility Component Storage Box	902-113

Die Cast Aluminum Enclosures


Item #: 900-162A



Item #: 900-162B




Item #: 900-162C



- Heavy-duty enclosures
- High-quality die cast aluminum
- Channeled walls for convenient PCB mounting
- Act as excellent heat sink

Description	Part No.
3.81"x1.96"x0.98"	900-162A
4.64"x2.36"x1.57"	900-162B
7.36"x4.21"x2.36"	900-162C

Utility Component Storage Box



Material: P.P.

- 7-3/8"x4-5/8"x7/8" (LxWxH)
- Material: P.P.



Terminals not included

Description	Part No.
Utility Component Storage Box	900-114

Instrument Cases

Item #: 900-164A



Item #: 900-164B

- Durable ABS cases allow for various PCB mounting positions
- Adhesive feet and screws are included
- 900-164B has ventilation slots and speaker recess

Description	Part No.
7.87"x6.29"x2.51"	900-164A
9.84"x7.48"x3.07"	900-164B


Insertion / Extraction Tool

- For inserting & extracting pins and sockets in connector housing



Description	Part No.
Insertion / Extraction Tool	900-065

Spudger



- Probe & Pick
- Tough nylon glass fiber construction
- Non-conductive - prevents shorting

Description	Part No.
Spudger	900-140

Parts Tubes

- 3-pack



Description	Part No.
Parts Tubes	900-091A

Metal Pronged Parts Grabber

Picks up and holds small parts in tight spaces.



Description	Part No.
4-Pronged Parts Grabber	902-225

PLCC Extractor

- Spring assisted
- Chip carrier extractor
- Extracts most PLCC's



Description	Part No.
PLCC Extractor	900-032

PLCC Extractor

A spring assisted chip carrier extraction tool, specially designed for the safe removal of PLCC's from sockets without damage to component parts.



Description	Part No.
PLCC Extractor	902-224

IC Extractor



Description	Part No.
IC Extractor	900-258

3-Pronged Parts Grabber

- Plunger opens prongs




Description	Part No.
3-Pronged Parts Grabber	900-094

Long Pick-up Tool with Magnet Tip (24-1/2")

Long Pick-Up Tool with Magnet Tip is an extendable magnetic tool for picking up small metallic objects from inaccessible areas. This Pick-Up Tool has a 24 1/2" flexible stem with a strong magnet at one end.

- Powerful magnet lifts 3.3 lb
- Ideal for home, shop, garage, work place etc.




Pick up small metallic objects from inaccessible areas



Description	Part No.
Long Pick-up Tool with Magnet Tip (24-1/2")	902-255

Push-button Pick-up Tool

- 902-256: Push-Button Pick-Up Tool has a 10-1/2" flexible stem with a small set of jaws at one end.
- 902-257: Long Push-Button Pick-Up Tool has a 23-1/2" flexible stem with a small set of jaws at one end.
- Ideal for home, shop, garage, work place etc.



Item #:902-257

Item #:902-256

Description	Part No.
Push-Button Pick-Up Tool (10 -1/2")	902-256
Long Push-Button Pick-Up Tool (23 -1/2")	902-257



Knife



Description	Part No.
Knife	900-257
Spare Blades (10 pc pack)	900-257B

Self-Loading Utility Knife

- Segmented, snap-off blades.
- Pocket clip.
- Self-loading - as one blade is discarded, simply pull the slide back and it loads another blade.
- Knife holds three blades.



Description	Part No.
Self-Loading Utility Knife	900-169
Replacement blade for 900-169 (6 pc pack)	900-169B

Electrician's Knife



Description	Part No.
Electrician's Knife	900-178

Utility folding Knife



Item #: 902-261



Item #: 902-253

Description	Part No.
Utility folding knife	902-253
Utility knife blades-100 pcs a pack	902-261

Fuse Puller



- Shock-proof durable plastic
- Serrated grip design to prevent slipping
- Safely removes 0-200A/250V and 0-100A/600V Cartridge fuses

Description	Part No.
Fuse Puller	900-177

7-In-1 Multi-Function Pocket Tool Key Chain



- Pocket-sized tools complete with spring-loaded pliers and almost any thing else you might need to get out of a bind.
- These tools include slotted and phillips screwdrivers, a serrated saw, a fruit knife, a mini LED flashlight, and a bottle opener.
- 7-in-1 function is all readily available to assist with your fix-it, snippet, tune-up, and tweak.

OAL: 4"

Description	Part No.
7-In-1 Multi-Function Pocket Tool Key Chain	902-230

Razor Hobbyist's Knife

Item #: 900-112



Item #: 900-113

Description	Part No.
Razor Hobbyist's Knife - Small	900-112
Replacement Blade for 900-112 (10 pc pack)	900-112B
Razor Hobbyist's Knife - Large	900-113
Replacement Blade for 900-113 (10 pc pack)	900-113B

5 Pc Hook Set


Contains 6 parts 5 different hooks which can be screwed in a handle.



Description	Part No.
5 Pc Hook Set	900-033

Hobby Vise

- Jaw width, 2.4"
- Opens to 2"
- Clamps to any surface up to 1" thick



Description	Part No.
Hobby Vise	900-049

Multi-Angle Swivel-Action Vacu-Vise

- Swivels 360° and tilts 90° to desired angle.
- 2-1/2" metal jaws open to 2-1/2" .
- Equipped with slide-on rubber jaw for fragile work.
- 6-1/4" triangular base.
- Aluminum die-cast construction.
- Light weight and durable.



Description	Part No.
Multi-Angle Swivel-Action Vacu-Vise	902-117

Magnetic, Telescopic Pick-up Tool

- Screwdriver handle style
- Magnetic tip
- Extends to approximately 16" long

Description	Part No.
Magnetic, Telescopic Pick-up Tool	900-017



Telescoping Magnetic Pick-up Tool

- Strong pick up force of 9 lbs.
- Allows access to "hand-to-reach" parts.
- Telescopes from 6-1/2" to 25-5/8"

Description	Part No.
Telescoping Magnetic Pick-up Tool	900-212



Inspection Mirror

Description	Part No.
Inspection Mirror	900-255



2" x 3" Rectangular Inspection Mirror

- Telescopes to 8-1/2"~19-1/4"

Description	Part No.
2" x 3" Rectangular Inspection Mirror	900-103



4 Piece Pick Set

- Stainless Steel
- One Straight, One Curve, and Two Hooked Tips

Description	Part No.
4 Piece Pick Set	900-205



Nibbling Tool

- Cuts up to AWG 18 soft steel or 1/16" Aluminum and Plastic



Description	Part No.
Nibbling Tool	900-215

Heat Gun



Item #: 900-119



Item #: 900-145

- Deluxe 2 temperature heat gun
- Ranges 1000°F and 600°F
- Hanging Hook

Description	Part No.
Heat Gun	900-119
4 pc nozzle accessories	900-145

Glue Gun



Item #: 900-115

Item #: 900-118A
Glue Sticks

Description	Part No.
Glue Gun (w/o Glue Sticks)	900-115
Glue Sticks Pkg of 6	900-118A

Heat Gun Kit

Best Value

General purpose heat gun deliver airflow and has 1.1" diameter nozzle. Well balanced and lightweight body. Two positions switch and temperature settings at 716°F and 932°F. Double insulated with an impact resistant heating element make the heat gun ideal for industrial applications.



Motor housing

1.1"Diameter nozzle

Two positions switch and temperature settings
at 716°F and 932°F

New



Blow molded case and 5 pcs accessories are included.

Description	Voltage	Wat	Teperature	Part No.
Heat Gun	110~120V 60Hz	I-1000W / II-1600W	I-380°C / II-500°C	SS-612A

6 In 1 Mini Hammer


- The 6 in 1 mini hammer with five different interchangeable tips: two round steel, one flat brass, one flat plastic and one tinner's steel.



Description	Part No.
6 In 1 Mini Hammer	902-116

Adjustable Wrenches

- Economy type
- 4, 6, and 8 inches
- Knurled adjustable screw
- Drop forged
- Insulated handles



Item #: 900-067

Item #: 900-068

Item #: 900-069

Description	Part No.
Adjustable Wrenches 4"	900-067
Adjustable Wrenches 6"	900-068
Adjustable Wrenches 8"	900-069
Adjustable Wrenches 10" (not shown)	900-223
Adjustable Wrenches 12" (not shown)	900-224

Mini-Combination Wrench Set

- 10 pieces quality wrenches



Description	Part No.
Inch Size	900-070
Closed end 7/16", 11/32", 3/8", 9/32", 5/16", 1/4", 16/64", 7/32", 5/32", 3/16"	
Open end 3/8", 5/16", 11/32", 1/4" 9/32", 15/64" 7/32", 13/64" 3/16", 5/32"	900-217
Metric Size	
Closed end 11, 10, 9, 8, 7, 6, 6, 5.5, 4.5, 4 mm	900-217
Open end 10, 9, 8, 7, 6, 5.5, 5, 4, 4, 4.5 mm	

Hammer

- 16 Ounce
- PVC Grip for Comfort



Item #: 900-179



Item #: 900-256

Description	Part No.
Heavy Duty Curved-Claw Hammer w/Fiberglass Handle	900-179
Ball-Peen Hammer	900-256

Multi-Stage Drill Bits (Titanium Coated)



Description	Spec.					Part No.
	No. of hole sizes per bit	Sizes range (hole dia.)	Pilot hole required	Electric drill size	Depth penetration for each step	
6 step 3/16-1/2"	6 in 1/16" increments	3/16 to 1/2"	NO	1/4" and larger	3/8"	900-183
8 step 9/16-1"	8 in 1/16" increments	9/16 to 1"	YES 1/2" or larger	1/2" and larger	1/8"	900-184
13 step 1/8-1/2"	13 in 1/32" increments	1/8 to 1/2"	NO	1/4" and larger	1/8"	900-185
10 step 13/16-1-3/8"	10 in 1/16" increments	13/16 to 1-3/8"	YES 1/4" or larger	1/2" and larger	1/8"	900-186
9 step 1/4-3/4"	9 in 1/16" increments	1/4 to 3/4"	NO	3/8" and larger	1/8"	900-187
12 step 3/16-7/8"	12 in 1/16" increments	3/16 to 7/8"	NO	3/8" and larger	1/8"	900-188

Automatic Center Punch




- For repetitive punching or riveting action
- Adjustable for light or heavy impact action
- Enlarged plastic handle for impact cushioning

Description	Part No.
Automatic Center Punch	900-158

5 PC Miniature File Set



- 5 mini files with plastic grips
- Each file is a different style



Unit: inch

Description	Part No.
5 Pc Miniature File Set	900-019

6 PC Hydraulic Punch Set




- with Hydraulic Piston

Conduit	
Nominal Size	Actual Size
1/2"	0.85"
3/4"	1.08"
1"	1.35"
1-1/4"	1.70"
1-1/2"	1.90"
2"	2.40"

Spring Hook

Can grab small spring and wires. Suitable for field service.




Part No. : 902-070


Part No. : 902-073

Description	Part No.
Spring Hook	902-070
	902-073

5 PC Heavy Duty Needle File Set



- OAL: 7.08"
- Cut Length: 3.34"
- OD: 0.27"



Unit: inch

Description	Part No.
5 PC Heavy Duty Needle File Set	900-216

4 PC Hydraulic Punch Set



- Punch and Die sets only

Conduit	
Nominal Size	Actual Size
2-1/2"	3"
3"	3-1/2"
3-1/2"	4"
4"	4-1/2"

Hydraulic Pump Available - P/N 900-010

Description	Part No.
6 PC Hydraulic Punch Set (1/2" to 2")	900-220

Description	Part No.
Punch and Die Sets only (2-1/2" to 4")	900-221

Alligator Clips

Description		Boot Color	Part No.
	Alligator Clip - Small (1.2") - 20 PC Pack	with no boot	902-027
		Red	902-026
		Black	902-036
	Alligator Clip - Small (1.4") - 20 PC Pack	with no boot	902-029
		Red	902-028
		Black	902-037
	20 Amp Battery Clip (2.6") - 5 PC Pack	with no boot	902-033
		Red	902-032
		Black	902-039
	Alligator Clip - Large Screw Type (2") - 20 PC Pack	with no boot	902-030
	Alligator Clip - Large (2") - 10 PC Pack	Red	902-031
		Black	902-038
	30 Amp Battery Clip (3") - 5 PC Pack	Red	902-034
		Black	902-040

17 PC Power Punch Kit

- Complete with 7 sets punches and dies
- Punches and dies hardened to C50-52
- Size: 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 9/32
- Will pierce up to 16 gauge steel



Description	Part No.
17 PC Power Punch Kit	900-046