

USB-4620 USB-4622 USB-4630

5-Port Isolated USB 2.0 Full-Speed Hub

5-Port USB 2.0 High-Speed Hub

4-Port Isolated USB 3.0 SuperSpeed™ Hub



USB-4620

FCC CE RoHS COMPLIANT (RECYCLED)



USB-4622

FCC CE RoHS COMPLIANT (RECYCLED)



USB-4630

FCC CE RoHS COMPLIANT (RECYCLED)

Features

- 5 downstream USB 2.0 ports
- Supports USB 2.0 full speed
- 3,000 V_{DC} voltage isolation for each downstream port
- Suitable for DIN rail mounting
- One lockable USB cable included
- 10 ~ 30 V_{DC} power input (power adapter not included)

Specifications

Connectivity

- Ports** 1 x Upstream (Type B)
5 x Downstream (Type A)
- Compatibility** USB 2.0 full speed
- Transfer Speed** 12 Mbps
- Supply Current** 500 mA max. per channel

General

- Housing** Plastic (ABS+PC)
- Dimensions (L x W x H)** 132 x 80 x 32 mm (5.2" x 3.15" x 1.26")
- DC Input** 10 ~ 30 V_{DC}
- Power Consumption** 24 V @ 36 mA
- Operating Temperature** 0 ~ 60 °C (32 ~ 140 °F)
- Storage Temperature** -20 ~ 70 °C (-4 ~ 158 °F)
- Storage Humidity** 5 ~ 95% RH non-condensing

Protection

- Isolation Protection** 3,000 V_{DC}

Ordering Information

- USB-4620-AE** 5-port isolated USB 2.0 full-speed hub

Accessories

- 96PSD-A40W24-MM** DIN rail power supply, 40 W, 24 V
- 1960004544** Wall mount bracket
- 1960005788** VESA mount bracket
- USB-LOCKCABLE-AE** Lockable USB 2.0 cable, 1 m, with screw kit

Features

- 5 downstream USB 2.0 ports
- Supports USB 2.0 high speed, USB 2.0 full speed, and USB 1.0
- 480 Mbps high-speed data transfer
- LED indicator
- Suitable for DIN rail mounting
- Lockable USB cable included
- 10 ~ 30 V_{DC} power input (power adapter not included)

Specifications

Connectivity

- Ports** 1 x Upstream (Type B)
5 x Downstream (Type A)
- Compatibility** USB 2.0 high speed, USB 2.0 full speed, USB 1.0
- Transfer Speed** 480 Mbps/12 Mbps/1.5 Mbps
- Supply Current** 500 mA max. per channel

General

- Housing** Plastic (ABS+PC)
- Dimensions (L x W x H)** 132 x 80 x 32 mm (5.2" x 3.15" x 1.26")
- DC Input** 10 ~ 30 V_{DC}
- Power Consumption** 24 V @ 36 mA
- Operating Temperature** 0 ~ 60 °C (32 ~ 140 °F)
- Storage Temperature** -20 ~ 70 °C (-4 ~ 158 °F)
- Storage Humidity** 5 ~ 95% RH non-condensing

Ordering Information

- USB-4622-BE** 5-port USB 2.0 high-speed hub

Accessories

- 96PSD-A40W24-MM** DIN rail power supply, 40 W, 24 V
- 1960004544** Wall mount bracket
- 1960005788** VESA mount bracket
- USB-LOCKCABLE-AE** Lockable USB 2.0 cable, 1 m, with screw kit

Features

- 2,500 V_{DC} voltage isolation for upstream ports
- 4 x downstream USB 3.0 SuperSpeed™ ports
- Can be powered via a USB bus or 10 ~ 30 V_{DC} external power source
- ESD protection up to ±8 kV (Level 3)
- Power status and downstream port speed LED indicators
- The world's first isolated USB 3.0 SuperSpeed Hub
- Up to 5 Gbps transfer speed
- Lockable USB 3.0 cable is included

Specifications

Connectivity

- Ports** 1 x Upstream (Type B)
4 x Downstream (Type A)
- Compatibility** USB 3.0 SuperSpeed (1)
- Transfer Speed** 5 Gbps shared by all downstream ports
- Load Current** External power: 900 mA max. per port
USB bus power: 700 mA max. shared by all ports (2)

General

- Housing** Plastic (ABS + PC)
- Dimensions (L x W x H)** 132 x 80 x 32 mm (5.2" x 3.15" x 1.26")
- Power Input** 10 ~ 30 V_{DC}
- Power Consumption** 760 mW (no load)
- Operating Temperature** 0 ~ 70 °C (32 ~ 158 °F) with external power
0 ~ 60 °C (32 ~ 140 °F) with USB bus power
- Storage Temperature** -20 ~ 70 °C (-4 ~ 158 °F)
- Storage Humidity** 5 ~ 95% RH (non-condensing)

Protection

- Isolation Protection** 2,500 V_{DC}
- ESD Protection** Contact discharge: ±4 kV (Level 2)
Air discharge: ±8 kV (Level 3)

Ordering Information

- USB-4630-AE** 4-port isolated USB 3.0 SuperSpeed™ hub
- 96PSD-A40W24-MM** DIN rail power supply, 40 W, 24 V