

D

C

B




A

D

C

B

A




SECTION:A-A
SCALE 2:1

- NOTES:
- MATERIAL:
 - HOUSING: HIGH TEMPERATURE THERMO PLASTIC,UL94V-0,COLOR:BLACK.
 - CONTACT: COPPER ALLOY.
 - SOLDER PEG AND LATCH:STAINLESS STEEL.
 - FINISH:

SOLDER PEG: GOLD FLASH ON 50u" MIN NICKEL UNDERPLATED ALL OVER.

CONTACT SOLDER AREA: GOLD FLASH ON SOLDER TAIL.

 - CONTACT AREA: GOLD FLASH ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
 - CONTACT AREA: 5u" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
 - CONTACT AREA: 10u" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
 - CONTACT AREA: 15U" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
 - CONTACT AREA: 30U" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
 - COPLANARITY: 0.10 MAX. (BEFORE SOLDERING)



- MATING: ① INSERTING(30°) → ② ROTATING → ③ FIXED
- UNMATING: ④ UNFIXED → ⑤ ROTATING → ⑥ WITHDRAWING

TAPE&REEL	BLACK	1.2V	30u"	260	2309412-5
TAPE&REEL	BLACK	1.2V	15u"	260	2309412-4
TAPE&REEL	BLACK	1.2V	10u"	260	2309412-3
TAPE&REEL	BLACK	1.2V	5u"	260	2309412-2
TAPE&REEL	BLACK	1.2V	GF	260	2309412-1
PACKING TYPE	HOUSING COLOR	POWER SUPPLY	FINISH	POS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	0.25
2 PLC	±	0.15
3 PLC	±	0.10
4 PLC	±	-
ANGLES	±	-
FINISH	±	-

DWN DAVID ZHAO 09SEP2016

CHK RICHARD MA 09SEP2016

APVD SIMON LI 09SEP2016

PRODUCT SPEC

108-115122

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

DDR4 SODIMM SOCKET
0.5mm PITCH 260POS
8.0mm HEIGHT REVERSE TYPE

SIZE A2

CAGE CODE 00779


DRAWING NO C=2309412

RESTRICTED TO -



SCALE 1:1

SHEET 1 of 3


REV 3




RECOMMEND PCB LAYOUT
THE TOLERANCE UNLESS SPECIFIED IS $\pm 0.05\text{MM}$



DETAIL:D
SCALE 2:1



DETAIL:C
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID ZHAO 09SEP2016 CHK RICHARD MA 09SEP2016 APVD SIMON LI 09SEP2016		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		NAME DDR4 SODIMM SOCKET 0.5mm PITCH 260POS 8.0mm HEIGHT REVERSE TYPE	
MATERIAL		FINISH			
		PRODUCT SPEC APPLICATION SPEC WEIGHT		SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C-2309412	RESTRICTED TO —
				SCALE 1:1	SHEET 2 of 3
				REV 3	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	-	-	-	-

D

C

B






A

D

C

B

A



250	2	500	*-2309412-*
PCS/ REEL	REEL/ CARTON	PCS/ CARTON	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID ZHAO 09SEP2016	TE Connectivity	
DIMENSIONS: mm		CHK RICHARD MA 09SEP2016		
TOLERANCES UNLESS OTHERWISE SPECIFIED		APVD SIMON LI 09SEP2016	NAME	
0 PLC ±		PRODUCT SPEC	DDR4 SODIMM SOCKET	
1 PLC ± -		APPLICATION SPEC	0.5mm PITCH 260POS	
2 PLC ± -		WEIGHT	8.0mm HEIGHT REVERSE TYPE	
3 PLC ± -		CUSTOMER DRAWING	SIZE CAGE CODE DRAWING NO	
4 PLC ± -		SCALE 1:1	A2 00779 C=2309412	
ANGLES ± -		SHEET 3 OF 3	RESTRICTED TO	
FINISH		REV 3		