

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301110024](#)  
**Status:** **Active**  
**Overview:** [Stringlights](#)  
**Description:** Pro-Yellow Stringlight, 150W, 12/2 TC2 with 2.43m Lead, 10 Sockets with Guards, Lamp-It-In-the-Box Packaging, Overall Length 30.48m (100.0'), cULus Listed

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E112216

**General**

Product Family Portable Lighting  
 Series [130111](#)  
 NEMA Configuration NEMA 1-15  
 NEMA Rating Rain Tight  
 Outlet None  
 Overview [Stringlights](#)  
 Product Name Pro-Yellow  
 Type String Lights  
 UPC 78678861202

**Physical**


Cord Length - Primary 2.43m (8.0')  
 Cord Length - Secondary 0.61m (2.0')  
 Depth N/A  
 Duty General  
 Guard Included Yes  
 Guard Type Polypropylene  
 Height N/A  
 Length 30.48m (100.0')  
 Material - Guard Polypropylene  
 Mounting Style Stringer  
 Net Weight 1.360/kg  
 Packaging Type Carton  
 Socket Construction Assembled

**Electrical**

Bulb Type Incandescent  
 Cord Type - Primary 12/2 TC  
 Lamp Type A21  
 Lamp Wattage - Maximum 150W  
 Lumens 1500  
 On/Off Switch No  
 Voltage (Fixture) - Maximum 120VAC 60 HZ

**Material Info**

Engineering Number 302SRL



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS Not Reviewed

ELV Not Relevant

RoHS Phthalates Not Reviewed

**Search Parts in this Series**

[130111 Series](#)