


K50-298⁷⁰ 302.472-542⁷⁰ 506

TERMINAL MATERIAL : BRASS
 INSULATION MATERIAL : VINYL
 DOUBLE CRIMP : WITH SLEEVE ON BARREL
 MAXIMUM ELECTRICAL RATING : 75°C 300 VOLTS

WIRE RANGE A.W.G.	MAXIMUM ELECTRIC CURRENT	INSULATION COLOR
22-16(1.25mm ²)	10 AMPERE	RED
16-14(2mm ²)	15 AMPERE	BLUE
12-10(5.5mm ²)	24 AMPERE	YELLOW



ITEM NO.	DIMENSION					
	W	a	L	C	B	T
FDD0.5-110(5)	3.3	0.5	16.0	1.0	7.8	0.25
FDD0.5-110(8)	3.3	0.8	16.0			
FDD1-110(5)	3.2	0.5	19.0	1.7	10.5	0.4
FDD1-110(8)	3.2	0.8	19.7			
FDD1-187(5)	5.03	0.5	19.7			
FDD1-187(8)	4.9	0.5	19.7			
FDD1-205	5.7	0.5	19.2	1.7	10.5	0.35
FDD1-250	6.6	0.8	21.2	1.7	10.5	0.4
FDD1-312	8.1	0.8	25.3			
FDD2-110(5)	3.2	0.5	19.7	2.3	10.5	0.3
FDD2-110(8)	3.2	0.8	19.7			
FDD2-187(5)	5.03	0.5	19.7	2.3	10.5	0.4
FDD2-187(8)	4.9	0.8	19.7			
FDD2-205	5.7	0.5	19.2	2.3	10.5	0.35
FDD2-250	6.6	0.8	21.0	2.3	10.5	0.4
FDD2-312	8.2	0.8	24.7			
FDD2-375	10.0	1.2	26.2	2.2	10.5	0.5
FDD5-110(5)	3.3	0.5	21.1	3.6	13.0	0.4
FDD5-110(8)	3.3	0.8	21.1			
FDD5-187(5)	4.9	0.5	21.1			
FDD5-187(8)	4.9	0.8	21.1			
FDD5-250	6.6	0.8	23.5	3.4	13.0	0.4
FDD5-375	10.0	1.2	28.5	3.4	13.0	0.5

第三角法 :



單位 UNIT: mm (in)

No:

設 變 內 容

日期

圖 名
NAME材 質
MATERIAL設 計
DESIGN

陳調慶

製 圖
DRAWN

黃 詩 涵

核 對
CHECK

計 算

產品編號
ITEM NO.

FDD全系列

數 量
PIECES比 例
SCALE圖 號
DRAWN NO:日 期
DATE

86/01/17