

KU-59-53

REVISIONS

REVISION	CHANGES
0	ER 4916 18 APR 67 J.G.
1	CN 5595A 10 JAN 68 J.B.
2	CN 14525A GA 2 JUN 75
3	CN 24645C M.A. 17 JUN 83
4	CN 26769 C M.Z.B. 21 JUNE 89

S-D

REF.

FINISH

SPEC. KER-10004

MATL.



SPEC.

UHF PLUG

DRAWN	J.G.	DATE	18 APR 67
APP.	K	DATE	11-1-67

KINGS ELECTRONICS
40 MARLBOROUGH ROAD
TUCKAHOE, N. Y.

KU-59-53



NOTES

1. K-GRIP FOR RG-58/U CABLE.
2. FOR CABLE TRIMMING USE KTJ-69 & KTD-34.
3. FOR CRIMPING USE DIE SIZE 01.
4. FOR CABLING INSTRUCTIONS SEE CP-410.
- 5.
6. SAME AS KU-59-46 EXCEPT FOR FINISH.

S-D

S-D

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES:
FRACTIONS $\pm .010$ DECIMALS $\pm .004$ ANGLES $\pm 0^\circ 20'$
TOLERANCE OF CONCENTRICITY ON ANY 2 DIAMETERS MAY NOT
EXCEED .004 INCHES.
2. REMOVE ALL BURRS. BREAK SHARP EDGES .003 MAX.
3. NO FILLETS PERMITTED
4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
5. ALL DIMENSIONS UNLESS OTHERWISE SPECIFIED

ITEM	QTY	DESCRIPTION	REMARKS
1	1	CRIMP CONTACT	
2	1	COUPLING NUT	U-59-02-4-M06
3	1	INSULATOR ASS'Y	
4	1	BODY	
5	1	K-GRIP	N-59-29-2-M06