






Fuer Kabel / For cable													
Gr.	Type Typ	ØD1 max.	ØD2 max.	ØD3 max.	ØD4 max.	ØD5	ØD6	ØD7	ØD8	Crimp Aussen/out	Crimp Innen/in		
8	RG 142 B/U; RG 400 /U	5,00	4,30	2,95	1,00	3,10	4,20	5,65	6,50	5,41	löten/ solder		
IMS CONNECTOR SYSTEMS		general tolerance ISO 2768 mH		scale: 5:1		Assembly instruction: M-184 Stripping dimension:							
					date	name	SN-Kabelwinkelstecker SN-Cable mount angle plug						
					generate	10 08 06						Schwaer	
					checked								
					Norm								
					047695			4177.SN.1420.08'					Rev a
design	a	Change acc sim 2	0108 07	RSch									
nr	rev	alteration	date	name									