

1 2 3 4 5 6 7 8

A

A

B

B

C

C

D





D

E

E

F

F



SPECIFICATION

1. Rated Voltage 12VDC
2. Operating Voltage 8~15VDC
3. Max. Rated Current 30mA/12VDC
4. Min. Sound Pressure Level 85dB/10cm
5. Resonant Frequency 2300±500Hz
6. Response Time 50ms
7. Case Material PBT
8. Operating Temperature -20~+70℃
9. Store Temperature -30~+80℃
10. Weight 2g

				KEPO KEPO ELECTRONIC CO., LTD. http://www.kepo.com.tw			
				Magnetic Buzzer			
				KPX-1212UB			
No.	DESCRIPTION	APPROVED	DATE				
TOLERANCES UNLESS NOTED OTHERWISE X .X XX .X XXX .X 90° FORMED -2° ANGLES -1° FIRST ANGLE PROJECTION		APPROVALS		DATE			
		DRAWN			UNIT	DWG NO.	
		CHECKED			mm	KP3.840.695	
		APPROVED		05.05.20	SCALE	NOT TO SCALE	VER 1.2