

SPEAR TIP pH ELECTRODE

Model : PE-06HD

ISO-9001, CE, IEC1010



LUTRON ELECTRONIC

The Art of Measurement

SPEAR TIP pH ELECTRODE

Model : PE-06HD

FEATURES

The "Spear Tip pH electrode" is perfect for those pH measurements in applications where sample piercing is required. Meat, sausage and cheese are ideal applications. The electrode features a very durable glass measuring spear packaged in a rugged virtually unbreakable epoxy body.

SPECIFICATIONS

Measuring Range	1 to 13 pH (typical 0 to 14 pH).
Operation Temperature	5 to 60 C degree (41 to 140 F degree)
Electrode Structure	Combination type.
Reference of pH Electrode	Ag/AgCl, Double Junction.
Response time	$\leq$ 2 minutes.
Body Material	Epoxy.
Connector	BNC.
pH value of zero mV	7 ± 1 pH.
Repetability	≥ 0.05 pH.
Mechanical Protection	With protection bottle on the electrode head.
Weight	68 g (including cable & socket).
Dimensions	Body length - 160 mm. Body Dia. - 12 mm. Cable length - 1000 mm.

* Appearance and specifications listed in this brochure are subject to change without notice.

0906-PE06HD