




Enclosure Receptacle SD 035



- Quick connections
- Available with or without fuse
- DIN rail mountable



Technical Data SD 035		Part No.	
Maximum ratings:	With fuse: 6.3 A at AC 250 V Without fuse (P/N 03504.0-01): 15 A at AC 125 V	Germany	6.3A fuse 03500.0-00
Fuse size:	Ø 5 x 20 mm, rated 6.3 A	France/Benelux	6.3A fuse 03501.0-00
Connection:	3 x AWG 20-16 (0.5-1.5 mm ²) push type terminals for stranded or rigid wire	Switzerland	6.3A fuse 03502.0-00
Mounting:	Clip for 35 mm DIN rail	Great Britain/Ireland	6.3A fuse 03503.0-00
Dimensions:	3.6 x 2.4 x 1.9" (92 x 62 x 48 mm)	USA/Canada	6.3A fuse 03504.0-00 No fuse, 125 V/15A max. 03504.0-01
Housing:	Plastic, UL94V-0	UL Recognized Component for USA/Canada part numbers only	
Protection class:	IP 20		
Protection type:	I (grounded)		
Operating/storage temperature:	-49 to 158°F (-45 to 70°C)		



SD035-11-05/US

Specifications are subject to change without notice. Suitability of this product for its intended use and any associated risks must be determined by the end customer/buyer in its final application.

STEGO, Inc. · 2270 Northwest Parkway · Suite 170 · Marietta, GA 30067 · Tel: (770) 984-0858 · Fax: (770) 984-0615
Toll free: 1-888-783-4611 (US & Canada only) · www.stegousa.com