

Search within category

GO

BUY NOW

DESIGN / INSTALL



VB0A1M2BM30P1

Vertical power strip 30 A, 120V, 24 IEC C-13 and 6 IEC C-19 receptacles, two 20 A single pole magnetic breaker/on-off switch with integral switch guard, and 10' power cord with NEMA L5-30P twist lock plug. UL and c-UL Listed. Dimensions: 66.3"H x 2.0"W x 2.0"D Breaker Doghouse add 1.44" (87.4mm) to overall depth (1683mm x 51mm x 51mm)

Specs

Packaging Details

Documents

★ Add to Favorites

Add to BOM

UL Listed	Yes
Rack PDU Type	Basic Rack PDU
Monitoring	None
Remote Outlet Switching	No
Mount Orientation	Vertical
Current Rating (Amps)	30A
Input Voltage	120V - Single Phase
Plug Type	NEMA L5-30P
Output Voltage	120V
Receptacle Type	IEC C-13 and IEC C-19
Total Number of Outlets	30
Depth (In.)	2.00
Depth (mm)	50.8
Height (In.)	66.25
Height (mm)	1682.8
Width (In.)	2.00
Width (mm)	50.8
Tool-Less Button Spacing (In.)	64.75
Tool-Less Button Spacing (mm)	1644.7
No. of Rack Spaces	0
Surge Suppression	No
Cable Length	3
RoHS Compliancy Status	Compliant
Min. Order Qty.	1