





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
F	00		G	CLARIFICATIONS	30JUN2009	JT	YP
			H	13 WAS 11.9 MAX. UPDATE NOTE 5 AND FORMAT	20OCT2011	JT	YP



10.90	6.17	55.32	13.56	15.37	10.74	61.11	52.43	66.93	RECEPTACLE WITH #20 SOCKET CONTACTS	50	5	MDP308GF - 50S2	6-135760-0
10.90	6.17	57.71	10.72	12.55	7.90	63.50	54.84	69.32	RECEPTACLE WITH #20 SOCKET CONTACTS	37	4	MDP308GF - 37S2	9-135760-5
10.90	6.17	41.30	10.72	12.55	7.90	47.04	38.38	53.04	RECEPTACLE WITH #20 SOCKET CONTACTS	25	3	MDP308GF - 25S2	5-135760-9
10.90	6.17	27.51	10.72	12.55	7.90	33.32	24.66	39.14	RECEPTACLE WITH #20 SOCKET CONTACTS	15	2	MDP308GF - 15S2	5-135760-8
10.90	6.17	19.28	10.72	12.55	7.90	24.99	16.33	30.81	RECEPTACLE WITH #20 SOCKET CONTACTS	9	1	MDP308GF - 9S2	9-135760-4
M±0.25	K±0.13	G±0.25	H±0.25	E±0.38	D±0.13	C±0.13	B±0.13	A±0.38	DESCRIPTION	NB POS.	SIZE	OLD P/N	P/N 2

SCALE 6:1

FLOATING BUSHING

SEE NOTES ON LAST SHEET

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
NOTE 3

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.13

1 PLC ±0.13

2 PLC ±0.13

3 PLC ±

4 PLC ±

ANGLES ±1

FINISH

NOTE 4

DWN
Thierry CORRIOU

CHK
Yves PETRONIN

APVD
Miguel FURIO

PRODUCT SPEC
-

APPLICATION SPEC
NOTE 7

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
SUB D RECEPTACLE WITH WIRE BUSHING MDP TYPE

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-135760


RESTRICTED TO
-

SCALE
2:1

SHEET
1

OF
5

REV
H



10.90	6.17	58.47	15.14	16.97	12.32	63.65	55.60	69.32	RECEPTACLE WITH #22 SOCKET CONTACTS	104	6	MDP308G - 66104S2	7-135760-9
10.90	6.17	55.32	13.56	15.37	10.74	61.11	52.43	66.93	RECEPTACLE WITH #22 SOCKET CONTACTS	78	5	MDP308G - 5078S2	9-135760-3
10.90	6.17	57.71	10.72	12.55	7.90	63.50	54.84	69.32	RECEPTACLE WITH #22 SOCKET CONTACTS	62	4	MDP308G - 3762S2	9-135760-1
10.90	6.17	41.30	10.72	12.55	7.90	47.04	38.38	53.04	RECEPTACLE WITH #22 SOCKET CONTACTS	44	3	MDP308G - 2544S2	6-135760-9
10.90	6.17	27.51	10.72	12.55	7.90	33.32	24.66	39.14	RECEPTACLE WITH #22 SOCKET CONTACTS	26	2	MDP308G - 1526S2	8-135760-8
10.90	6.17	19.28	10.72	12.55	7.90	24.99	16.33	30.81	RECEPTACLE WITH #22 SOCKET CONTACTS	15	1	MDP308G - 915S2	8-135760-6
10.90	6.17	55.32	13.56	15.37	10.74	61.11	52.43	66.93	RECEPTACLE WITH #20 SOCKET CONTACTS	50	5	MDP308G - 50S2	5-135760-7
10.90	6.17	57.71	10.72	12.55	7.90	63.50	54.84	69.32	RECEPTACLE WITH #20 SOCKET CONTACTS	37	4	MDP308G - 37S2	5-135760-6
10.90	6.17	41.30	10.72	12.55	7.90	47.04	38.38	53.04	RECEPTACLE WITH #20 SOCKET CONTACTS	25	3	MDP308G - 25S2	5-135760-5
10.90	6.17	27.51	10.72	12.55	7.90	33.32	24.66	39.14	RECEPTACLE WITH #20 SOCKET CONTACTS	15	2	MDP308G - 15S2	8-135760-3
10.90	6.17	19.28	10.72	12.55	7.90	24.99	16.33	30.81	RECEPTACLE WITH #20 SOCKET CONTACTS	9	1	MDP308G - 9S2	5-135760-4
M±0.25	K±0.13	G±0.25	H±0.25	E±0.38	D±0.13	C±0.13	B±0.13	A±0.38	DESCRIPTION	NB POS.	SIZE	OLD P/N	P/N 2

SEE NOTES ON LAST SHEET

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
NOTE 3

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±0.13
1 PLC	±0.13
2 PLC	±0.13
3 PLC	±
4 PLC	±
ANGLES	±1
FINISH	NOTE 4

DWN
Thierry CORRIOU
CHK
Yves PETRONIN
APVD
Miguel FURIO

21APR2004
21APR2004
21APR2004

PRODUCT SPEC
-
APPLICATION SPEC
NOTE 7
WEIGHT
-

TE Connectivity

NAME
SUB D RECEPTACLE WITH WIRE BUSHING MDP TYPE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-135760	-

CUSTOMER DRAWING


SCALE 2:1

SHEET 2 OF 5

REV H

1470-19 (3/11)

LOC		DIST		REVISIONS					
F		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					-	SEE SHEET 1	-	-	-



10.90	6.17	58.47	15.14	16.97	12.32	63.65	55.60	69.32	RECEPTACLE, HIGH DENSITY	104	6	MDP308G - 66104S2 - 001	8-135760-0
10.90	6.17	55.32	13.56	15.37	10.74	61.11	52.43	66.93	RECEPTACLE, HIGH DENSITY	78	5	MDP308G - 5078S2 - 001	9-135760-2
10.90	6.17	57.71	10.72	12.55	7.90	63.50	54.84	69.32	RECEPTACLE, HIGH DENSITY	62	4	MDP308G - 3762S2 - 001	9-135760-0
10.90	6.17	41.30	10.72	12.55	7.90	47.04	38.38	53.04	RECEPTACLE, HIGH DENSITY	44	3	MDP308G - 2544S2 - 001	8-135760-9
10.90	6.17	27.51	10.72	12.55	7.90	33.32	24.66	39.14	RECEPTACLE, HIGH DENSITY	26	2	MDP308G - 1526S2 - 001	8-135760-7
10.90	6.17	19.28	10.72	12.55	7.90	24.99	16.33	30.81	RECEPTACLE, HIGH DENSITY	15	1	MDP308G - 915S2 - 001	8-135760-5
10.90	6.17	55.32	13.56	15.37	10.74	61.11	52.43	66.93	RECEPTACLE	50	5	MDP308G - 50S2 - 001	4-135760-5
10.90	6.17	57.71	10.72	12.55	7.90	63.50	54.84	69.32	RECEPTACLE	37	4	MDP308G - 37S2 - 001	4-135760-4
10.90	6.17	41.30	10.72	12.55	7.90	47.04	38.38	53.04	RECEPTACLE	25	3	MDP308G - 25S2 - 001	4-135760-6
10.90	6.17	27.51	10.72	12.55	7.90	33.32	24.66	39.14	RECEPTACLE	15	2	MDP308G - 15S2 - 001	4-135760-3
10.90	6.17	19.28	10.72	12.55	7.90	24.99	16.33	30.81	RECEPTACLE	9	1	MDP308G - 9S2 - 001	4-135760-2
M±0.25	K±0.13	G±0.25	H±0.25	E±0.38	D±0.13	C±0.13	B±0.13	A±0.38	DESCRIPTION	NB POS	SIZE	OLD P/N	P/N 2

SEE NOTES ON LAST SHEET

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
NOTE 3

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.13

1 PLC ±0.13

2 PLC ±0.13

3 PLC ±

4 PLC ±

ANGLES ±1

FINISH NOTE 4

DWN 21APR2004
Thierry CORRIOU

CHK 21APR2004
Yves PETRONIN

APVD 21APR2004
Miguel FURIO

PRODUCT SPEC
-

APPLICATION SPEC
NOTE 7

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
SUB D RECEPTACLE
WITH WIRE BUSHING
MDP TYPE

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-135760

RESTRICTED TO
-

SCALE 2:1

SHEET 3 OF 5

REV H

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

Tyco Electronics AMP GmbH

ALL RIGHTS RESERVED.

LOC

F

DIST

00

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

-


SEE SHEET 1

-


-

-


MATING FACE OF PLUG SHOWN
CONFIGURATIONS FOR #20 CONTACTS




9 POSITION MS18273-1
SHELL SIZE 1




15 POSITION MS18274-1
SHELL SIZE 2



25 POSITION MS18275-1
SHELL SIZE 3




37 POSITION MS18276-1
SHELL SIZE 4




50 POSITION MS18277-1
SHELL SIZE 5


CONFIGURATIONS FOR #22 CONTACTS
MATING FACE OF PLUG SHOWN




15 POSITION MS18273-2
SHELL SIZE 1




26 POSITION MS18274-2
SHELL SIZE 2




44 POSITION MS18275-2
SHELL SIZE 3



62 POSITION MS18276-2
SHELL SIZE 4



78 POSITION MS18277-2
SHELL SIZE 5




104 POSITION MS14004-1
SHELL SIZE 6

SEE NOTES ON LAST SHEET

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

NOTE 3

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±0.13
1 PLC ±0.13
2 PLC ±0.13
3 PLC ±
4 PLC ±
ANGLES ±1

FINISH

NOTE 4

DWN 21APR2004

Thierry CORRIOU

CHK 21APR2004

Yves PETRONIN

APVD 21APR2004

Miguel FURIO

PRODUCT SPEC

-

APPLICATION SPEC

NOTE 7

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

SUB D RECEPTACLE
WITH WIRE BUSHING
MDP TYPE

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-135760

RESTRICTED TO

-

SCALE 1:1

SHEET 4 OF 5

REV H

4

3

2

1


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	Tyco Electronics AMP GmbH	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
F	00		-	SEE SHEET 1	-	-

THIS CONNECTOR MEETS THE REQUIREMENTS OF MIL-DTL-24308

PART NUMBER FOR ORDERING

- 3- MATERIALS :
- SHELL : STEEL,CD PLATED
 - HOUSING : PBT,GLASS FILLED,UL94VO
 - RETAINING CLIP : STAINLESS STEEL
 - GROMMET AND INTERFACIAL SEAL : FLUOROSILICONE ELASTOMER
 - SEALING COMPOUND : RTV
 - CONTACT:COPPER ALLOY,GOLD PLATED OVER NICKEL
- 4- CABLES EXTERNAL DIAMETER FOR CONTACTS #20 : $\varnothing 0.85$ to $\varnothing 1.83$
CABLES EXTERNAL DIAMETER FOR CONTACTS #22 : $\varnothing 1.37$ MAX
- 5- CONNECTOR MARKING:
- . MANUFACTURER IDENTIFICATION
 - . PART NUMBER
 - . DATE-CODE
- 6- INSERT ARRANGEMENT PER MIL-DTL-24308
- 7- FOR CONTACT CRIMPING INSTRUCTION SHEET REFER TO SPEC IS 7516
FOR CONTACT INSTALATION/ REMOVAL INSTRUCTION SHEET REFER TO SPEC IS 7508
- 8- #20 SOCKET CRIMP CONTACT P/N: 205090-1
#20 PIN CRIMP CONTACT P/N: 205089-1
- #22D SOCKET CRIMP CONTACT P/N: 204351-1
#22D PIN CRIMP CONTACT P/N: 204370-2
- 9- INSERTION/EXTRACTION TOOL P/N: 91067-2
INSERTION/EXTRACTION TOOL P/N: 91067-1
- 10- CRIMP WITH HAND TOOL: 601966-1+ DIE INSERT : 601966-4
CRIMP WITH HAND TOOL: M22520/02-01 + POSITIONNER : M22520/02-06

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Thierry CORRIOU 21APR2004	 TE Connectivity					
		CHK Yves PETRONIN 21APR2004						
DIMENSIONS: mm		APVD Miguel FURIO 21APR2004	NAME SUB D RECEPTACLE WITH WIRE BUSHING MDP TYPE					
		PRODUCT SPEC - 						
		APPLICATION SPEC NOTE 7	SIZE A3	CAGE CODE 00779	DRAWING NO C-135760		RESTRICTED TO -	
MATERIAL NOTE 3		FINISH NOTE 4	WEIGHT -					
			CUSTOMER DRAWING			SCALE 1 : 1	SHEET 5 OF 5	REV H