

PNEUMATIC CRIMPERS

PC24-14B—BENCH CRIMPER, TRAPEZOID CRIMPER, SIDE & FRONT ENTRY

	RANGE	24-14 AWG (0.25-2.5MM ²)
	LENGTH	5.5x7.8x2.8 INCHES (140x200x70 MM)
	WEIGHT	2.2 POUNDS (1000G)
	PRESSURE	58 PSI (4 BAR)

PC24-14H—HAND CRIMPER, TRAPEZOID CRIMPER, SIDE & FRONT ENTRY

	RANGE	24-14 AWG (0.25-2.5MM ²)
	LENGTH	1.73 x 7.88 INCHES (44 x 200MM)
	WEIGHT	14.1 OUNCES (400G)
	PRESSURE	58 PSI (4 BAR)

PC12-8B—BENCH CRIMPER, TRAPEZOID CRIMPER, SIDE & FRONT ENTRY

	RANGE	12-8 AWG (4-10MM ²)
	LENGTH	5.5x7.8x2.8 INCHES (140x200x70 MM)
	WEIGHT	2.2 POUNDS (1000G)
	PRESSURE	58 PSI (4 BAR)

PC12-8B—HAND CRIMPER, TRAPEZOID CRIMPER, SIDE & FRONT ENTRY

	RANGE	12-8 AWG (4-10MM ²)
	LENGTH	1.73 x 7.88 INCHES (44 x 200MM)
	WEIGHT	14.1 OUNCES (400G)
	PRESSURE	58 PSI (4 BAR)

ACCESSORIES

	PC1	BALANCER
	PC2	MAGNETIC TOOL HOLDER