

040/070 Series Hybrid (Continued)

Receptacle Contact (Side Lock Type)						
Type of Contact	Wire Range	Wire Ins. Diameter	Finish	Strip Form	Loose Piece	Hand Tool No.
040 Series Application Specification: 114-5159	0.3-0.85mm ² (AWG#22-18)	ø1.1-1.8mm	KLF-5/Pre-Tin	175265-1	—	934192-1
			KLF-5/Sel. Gold	175266-2	179418-2	
070 Series Application Specification: 114-5160	0.3-0.85mm ² (AWG#22-18)	ø1.1-1.8mm	Brass/Pre-Tin	175268-1	—	934195-1
			Brass/Sel. Gold	175275-2	—	
	0.5-1.25mm ² (AWG#20-16)	ø1.8-2.5mm	Brass/Pre-Tin	175269-1	—	934196-1
			Brass/Sel. Gold	175276-2	179426-2	

Plug Housing(Side Lock Type)	
12 P ☐-917975-☐ ☐-178845-☐ Mating Cap 76 Position: ☐-178780-☐ (see page 41)	☐-917978-☐ ☐-178881-☐ Mating Cap 34 Position: ☐-175444-☐ (see page 35) 38 Position: ☐-178093-☐ (see page 36) 54 Position: ☐-175448-☐ (see page 39)