

GS1T50

BURNDY® PRODUCTS

GS1T50

GS1T50 : 3/8-1" CU GRD STRAP .05



ACTIVE

[Assistant](#)[Add to Favorites](#)
[✉ Email Datasheet](#)
[🖨 Print Datasheet](#)

FCI Brings You More

[✉ > Contact our sales/technical support](#)
[📄 > Sample request](#)
[€ > Price request](#)

Specifications

[Download document](#)

| General                    | Dimensional | Physical | Approvals / Certifications | Other Features |
|----------------------------|-------------|----------|----------------------------|----------------|
| General                    |             |          |                            |                |
| Armored Cable              |             |          | No                         |                |
| Dimensional                |             |          |                            |                |
| Length (in)                |             |          | 0.05 in.                   |                |
| Pipe Size                  |             |          | 1 in.<br>3/8 in.           |                |
| Pipe Size (Range)          |             |          | 3/8 in. to 1 in.           |                |
| Physical                   |             |          |                            |                |
| Material/Body              |             |          | Pure Annealed Copper       |                |
| Type of Hardware           |             |          | Zinc Plated                |                |
| Approvals / Certifications |             |          |                            |                |
| UL Listed                  |             |          | No                         |                |
| CSA Certified              |             |          | No                         |                |
| Other Features             |             |          |                            |                |
| UPC                        |             |          | 78181014250                |                |
| Key word                   |             |          | groundstraps               |                |