




DIN 7981 F

~ISO 7049

450 HV

Standard withdrawn



BN 33

Phillips pan head tapping screws

form H, with flat end type F

Steel case-hardened 450 HV

zinc plated blue

- ~UNI 6954 B
- ~CSN 021235



ISO 4042

Quenched and tempered fasteners ≥ 360 HV and tempered case-hardened fasteners with electroplated coatings: Susceptible to hydrogen embrittlement!
Further notice to residual risks can be found in the introduction section.


[3D Cadenas](#)

Article#	d ₁	d ₂ max.	k max.		m~	L
1037218	ST 2,2	4,2	1,8	1	2,6	4,5
1037226						6,5
1037234						9,5
1037250						13
1037277						16
1037285	ST 2,9	5,6	2,2	1	3	6,5
1037293						9,5
1037307						13
1037315						16
1037323						19
1669737	ST 3,5	6,9	2,6	2	4,2	6,5
1037331						9,5
1037358						13
1037366						16
1037374						19
1037439	(ST 3,9)	7,5	2,8	2	4,4	9,5
1037447						13
1037455						16
1037463						19
1037528	ST 4,2	8,2	3,05	2	4,6	9,5
1037536						13
1037579						16
1037595						19
1037617						25
1037625						32