

Honeywell Sensing and Control

Search

→

narrow your search

- Products
- Controls Monitoring and Lighting (354)
  - Machine Safety (1726)
  - Sensors (7074)
  - Switches (9814)

- Technology
- Control and Instrumentation (1063)
  - Electromechanical (9357)
  - Microstructure (2328)
  - Optical/Infrared (1077)
  - Thick Film (1764)
  - More...

Need Help?

Click here to contact us →

364P10K Trimmers

(Home : Products)



Actual product appearance may vary.

364 Series Trimmer, 10 kOhm, 0.5 W, 25 Turns, Square Body, Horizontal Shaft

Sales & Service →

Distributor Inventory →

Overview

Specs

Documentation

Application Notes

Product Specifications

|                         |                           |
|-------------------------|---------------------------|
| Product Type            | Trimmer                   |
| Watts                   | 0.5 W                     |
| Turns                   | 25                        |
| Element Type            | Cermet                    |
| Resistance Value        | 10 kOhm                   |
| Resistance Tolerance    | ± 10 %                    |
| Temperature Coefficient | ± 100 ppm/ °C             |
| Body                    | 9.53 mm [0.375 in] square |
| Shaft Location          | Horizontal                |
| Rotational Life         | 200 cycles                |
| Series Name             | 364                       |
| Availability            | Global                    |
| UNSPSC Code             | 4111363300                |
| UNSPSC Commodity        | 4111363300 Potentiometers |