


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
FT	0		S2	REVISED PER ECO-11-004820	11MAR11	RK
						APVD
						HMR



- 1

NYLON, UL 94V-O RATED, RED.
- 2

BRASS PER ASTM B36.
- 3

3.81um [.000150] MIN TIN OVER 2.54um [.000100] MIN COPPER.
- 4

0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81um [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.
- 5

SELECTIVELY LOADED CONTACTS IN POSITIONS 1 THRU 5, 7 THRU 12.
- 6

3.81um [.000150] MIN TIN OVER 2.54um [.000100] MIN COPPER.

- 7

0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81um [.000150] MIN TIN FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.
- 8

OBsolete PARTS: OBsolete CIS STREAMLINING PER D.RENAUD/D.SINISI

8 SUPERSEDED BY 1-207120-2

6	YES	5	1-207120-2
7	NO		1-207120-1
6	NO		1-207120-0
6	YES		207120-9
7	YES		207120-8
3	YES	5	207120-7
4	NO		207120-4
4	YES		207120-3
3	NO		207120-2
3	YES		207120-1
CONTACT FINISH		MOUNTING TABS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	03/11/92	TE Connectivity			
		CHK	3-17-92				
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-10033			
				APPLICATION SPEC			
MATERIAL HOUSING: 1		FINISH CONTACT: SEE TABLE		WEIGHT	-	SIZE A2	CAGE CODE 00779
				DRAWING NO	C=207120	RESTRICTED TO	-
CUSTOMER DRAWING				SCALE	4:1	SHEET	1 OF 1
				REV	S2		