

REV.	DESCRIPTION	DATE
A	RELEASE	2012.11.12

NOTES:

Insulator Material: PBT, UL 94V-0

Contact Plating: flash gold

Contact Material: Brass







Current Rating : 1A AC,DC

Contact Resistance: 20MΩ Max.

Dielectric Withstanding: AC 500V

Insulator Resistance: 1000MΩ Min.

Operating Temp.: -40°C~+105°C



NUMBER OF POSITIONS	DIMENSION	
	A	B
06	4.0	11.2
08	6.0	13.2
10	8.0	15.2
12	10.0	17.2
14	12.0	19.2
16	14.0	21.2
18	16.0	23.2
20	18.0	25.2
22	20.0	27.2
24	22.0	29.2
26	24.0	31.2
28	26.0	33.2
30	28.0	35.2
34	32.0	39.2
36	34.0	41.2
40	38.0	45.2
44	42.0	49.2
50	48.0	55.2

UNLESS TOLERANCE		DRAW	BY
GENERAL	ANGLE	DESIGN	BY

X. ± 0.30	X.° ± 3.0°	CHECK	BY
.X ± 0.20	.X° ± 2.0°		
.XX ± 0.15	.XX° ± 1.0°	APPROVE	BY
.XXX ± 0.10	.XXX° ± 0.5°		

CnC Tech,LLC

Port NO.

3130-XX-0101-00



SCALE	SHEET	UNIT
1:1	1/1	MM

DRW NO:

REV: A